


# Novastar Rear Panel With Cable Ducting

## Power Utilities



Novastar Rear Panel with 3 U cable ducting for improved cable management.

## CERTIFICATIONS



## CARACTERISTICI

Cable ducting and door hinge bracket

Cable ducting can be fitted at top or bottom

2 twist-locking catches (Torx T30, with 1/4 turn)

Incl. grounding

St, 1 mm

3 U cable ducting for cabinet heights 16, 20, 38, 47 U; 4 U cable ducting for cabinet heights 25, 34, 43 U

## SPECIFICAȚII

Table 1/2

| Număr de catalog | Rack Height | Height  | Width  | Color      | Color Code | Product Type       |
|------------------|-------------|---------|--------|------------|------------|--------------------|
| 25230-430        | 16 U        | 733 mm  | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-430        | 16 U        | 733 mm  | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-434        | 20 U        | 911 mm  | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-434        | 20 U        | 911 mm  | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-439        | 25 U        | 1133 mm | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-439        | 25 U        | 1133 mm | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-448        | 34 U        | 1534 mm | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-448        | 34 U        | 1534 mm | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-452        | 38 U        | 1711 mm | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-452        | 38 U        | 1711 mm | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-457        | 43 U        | 1933 mm | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-457        | 43 U        | 1933 mm | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-461        | 47 U        | 2111 mm | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-461        | 47 U        | 2111 mm | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |

Table 2/2

| Număr de catalog | Type       |
|------------------|------------|
| 25230-430        | Rear Panel |
| 26230-430        | Rear Panel |

| Număr de catalog | Type       |
|------------------|------------|
| 25230-434        | Rear Panel |
| 26230-434        | Rear Panel |
| 25230-439        | Rear Panel |
| 26230-439        | Rear Panel |
| 25230-448        | Rear Panel |
| 26230-448        | Rear Panel |
| 25230-452        | Rear Panel |
| 26230-452        | Rear Panel |
| 25230-457        | Rear Panel |
| 26230-457        | Rear Panel |
| 25230-461        | Rear Panel |
| 26230-461        | Rear Panel |

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**