

Varistar CP Base Plate, One-Piece

Power Utilities

The base plate is solid and covers the base of the cabinet.

CARACTERISTICI

The base plate is solid and covers the base of the cabinet

Is assembled from outside

SPECIFICAȚII

Table 1/2

Număr de catalog	Width	Depth	Protection Rating	Color	Color Code	Complies With
21630-320	600 mm	300 mm		Black Grey	RAL 7021	
21630-628	600 mm	300 mm		Black Grey	RAL 7021	
21630-322	600 mm	600 mm		Black Grey	RAL 7021	
21630-323	600 mm	800 mm		Black Grey	RAL 7021	
21630-324	600 mm	900 mm		Black Grey	RAL 7021	
21630-325	600 mm	1000 mm		Black Grey	RAL 7021	
21630-326	600 mm	1100 mm		Black Grey	RAL 7021	
21630-327	600 mm	1200 mm		Black Grey	RAL 7021	
21630-629	600 mm	600 mm		Black Grey	RAL 7021	

Număr de catalog	Width	Depth	Protection Rating	Color	Color Code	Complies With
21630-630	600 mm	800 mm		Black Grey	RAL 7021	
21630-631	600 mm	900 mm		Black Grey	RAL 7021	
21630-632	600 mm	1000 mm		Black Grey	RAL 7021	
21630-633	600 mm	1100 mm		Black Grey	RAL 7021	
21630-634	600 mm	1200 mm		Black Grey	RAL 7021	
21630-826	600 mm	600 mm	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-827	600 mm	800 mm	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-828	600 mm	900 mm	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-829	600 mm	1000 mm	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-830	600 mm	1100 mm	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-831	600 mm	1200 mm	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-330	800 mm	600 mm		Black Grey	RAL 7021	
21630-635	800 mm	600 mm		Black Grey	RAL 7021	
21630-832	800 mm	600 mm	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-331	800 mm	800 mm		Black Grey	RAL 7021	
21630-332	800 mm	900 mm		Black Grey	RAL 7021	
21630-333	800 mm	1000 mm		Black Grey	RAL 7021	
21630-334	800 mm	1100 mm		Black Grey	RAL 7021	

Număr de catalog	Width	Depth	Protection Rating	Color	Color Code	Complies With
21630-335	800 mm	1200 mm		Black Grey	RAL 7021	
21630-636	800 mm	800 mm		Black Grey	RAL 7021	
21630-637	800 mm	900 mm		Black Grey	RAL 7021	
21630-638	800 mm	1000 mm		Black Grey	RAL 7021	
21630-639	800 mm	1100 mm		Black Grey	RAL 7021	
21630-640	800 mm	1200 mm		Black Grey	RAL 7021	
21630-833	800 mm	800 mm	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-834	800 mm	900 mm	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-835	800 mm	1000 mm		Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-836	800 mm	1100 mm	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-837	800 mm	1200 mm	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Număr de catalog	Material	Product Type	Works With
21630-320	Oțel	Cabinet/Rack Base	
21630-628	Oțel	Cabinet/Rack Base	
21630-322	Oțel	Cabinet/Rack Base	
21630-323	Oțel	Cabinet/Rack Base	
21630-324	Oțel	Cabinet/Rack Base	
21630-325	Oțel	Cabinet/Rack Base	

Număr de catalog	Material	Product Type	Works With
21630-326	Oțel	Cabinet/Rack Base	
21630-327	Oțel	Cabinet/Rack Base	
21630-629	Oțel	Cabinet/Rack Base	
21630-630	Oțel	Cabinet/Rack Base	
21630-631	Oțel	Cabinet/Rack Base	
21630-632	Oțel	Cabinet/Rack Base	
21630-633	Oțel	Cabinet/Rack Base	
21630-634	Oțel	Cabinet/Rack Base	
21630-826	Oțel	Cabinet/Rack Base	Varistar CP
21630-827	Oțel	Cabinet/Rack Base	Varistar CP
21630-828	Oțel	Cabinet/Rack Base	Varistar CP
21630-829	Oțel	Cabinet/Rack Base	Varistar CP
21630-830	Oțel	Cabinet/Rack Base	Varistar CP
21630-831	Oțel	Cabinet/Rack Base	Varistar CP
21630-330	Oțel	Cabinet/Rack Base	
21630-635	Oțel	Cabinet/Rack Base	
21630-832	Oțel	Cabinet/Rack Base	Varistar CP
21630-331	Oțel	Cabinet/Rack Base	

Număr de catalog	Material	Product Type	Works With
21630-332	Oțel	Cabinet/Rack Base	
21630-333	Oțel	Cabinet/Rack Base	
21630-334	Oțel	Cabinet/Rack Base	
21630-335	Oțel	Cabinet/Rack Base	
21630-636	Oțel	Cabinet/Rack Base	
21630-637	Oțel	Cabinet/Rack Base	
21630-638	Oțel	Cabinet/Rack Base	
21630-639	Oțel	Cabinet/Rack Base	
21630-640	Oțel	Cabinet/Rack Base	
21630-833	Oțel	Cabinet/Rack Base	Varistar CP
21630-834	Oțel	Cabinet/Rack Base	Varistar CP
21630-835	Oțel	Cabinet/Rack Base	Varistar CP
21630-836	Oțel	Cabinet/Rack Base	Varistar CP
21630-837	Oțel	Cabinet/Rack Base	Varistar CP

DETALII SUPLIMENTARE DESPRE PRODUS

This base plate is used for applications which don't require cable entry from the base.

Please purchase the grounding kit separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și

avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE