

Varistar CP Deco Frame

Power Utilities

CARACTERISTICI

19" plane is integrated into decorative frame

Aluminum, decorative frame for open cabinet

Open at front, no door can be fitted

SPECIFICAȚII

Table 1/2

Număr de catalog	Rack Height	Height	Width	Color	Color Code	Frame Material
21630-309	24 U	1200 mm	600 mm	Black Grey	RAL 7021	Oțel
21630-310	29 U	1400 mm	600 mm	Black Grey	RAL 7021	Oțel
21630-311	33 U	1600 mm	600 mm	Black Grey	RAL 7021	Oțel
21630-312	38 U	1800 mm	600 mm	Black Grey	RAL 7021	Oțel
21630-313	42 U	2000 mm	600 mm	Black Grey	RAL 7021	Oțel
21630-314	47 U	2200 mm	600 mm	Black Grey	RAL 7021	Oțel

Table 2/2

Număr de catalog	Material	Product Type	Protection Rating	Type	Works With
21630-309	Aluminiu	Cabinet/Rack Frame	IP20	Deco Frame	Varistar CP

Număr de catalog	Material	Product Type	Protection Rating	Type	Works With
21630-310	Aluminiu	Cabinet/Rack Frame	IP20	Deco Frame	Varistar CP
21630-311	Aluminiu	Cabinet/Rack Frame	IP20	Deco Frame	Varistar CP
21630-312	Aluminiu	Cabinet/Rack Frame	IP20	Deco Frame	Varistar CP
21630-313	Aluminiu	Cabinet/Rack Frame	IP20	Deco Frame	Varistar CP
21630-314	Aluminiu	Cabinet/Rack Frame	IP20	Deco Frame	Varistar CP

DETALII SUPLIMENTARE DESPRE PRODUS

Please purchase the grounding kit separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE