

19" Pusher Fan, 2 U, Axial

Fan tray with integrated pusher fan.



CERTIFICATIONS



CARACTERISTICI

Contact protection in accordance with DIN EN ISO 13857

Integrated air deflector prevents heat buildup in the assemblies mounted below

Can be adapted to sub racks

Optionally with additional rear fan, 2 U, for active cooling of assemblies beneath the pusher fan

SPECIFICAȚII

Table 1/1

Număr de catalog	Input Voltage AC	Input Voltage DC	Package Quantity	Finish	Material	Quick Ship
19713-540			1	Aluminum-Zinc Plated	Oțel, Polypropylene	No
10713-518	230V		1	Aluminum-Zinc Plated	Oțel, Polypropylene	No
10713-537		24V min	1	Aluminum-Zinc Plated	Oțel, Polypropylene	No

Număr de catalog	Input Voltage AC	Input Voltage DC	Package Quantity	Finish	Material	Quick Ship
10713-536	115V		1	Aluminum-Zinc Plated	Oțel, Polypropylene	No
10713-534	230V		1	Aluminum-Zinc Plated	Oțel, Polypropylene	No
10713-529		24V min	1	Aluminum-Zinc Plated	Oțel, Polypropylene	No
10713-520	115V		1	Aluminum-Zinc Plated	Oțel, Polypropylene	No
10713-526	230V		1	Aluminum-Zinc Plated	Oțel, Polypropylene	No

DETALII SUPLIMENTARE DESPRE PRODUS

Please order mains cable separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE