


Assembly Parts for Rugged Components



Assembly parts with thread-locking compound for rugged Side Panel, horizontal rail, cover plates, rear angle.

CERTIFICATIONS



CARACTERISTICI

Screws for the following fixings: Rugged side panel - horizontal rail, Rugged side panel - cover plate, Rugged side panel - rear angle

SPECIFICAȚII

Product Type: Assembly Kit

Product Family: EuropacPRO

Table 1/2

Număr de catalog	Type	Length	Package Quantity	Thread Size	Finish	Material
24566-105	Countersunk Screw	7mm	100	M4		Stainless Steel
24560-140	Square Nut		100		Oțel Zincat	Oțel
24566-106	Countersunk Screw	10mm	100	M4		Stainless Steel
24566-101	Countersunk Screw	14mm	100	M4		Stainless Steel

Număr de catalog	Type	Length	Package Quantity	Thread Size	Finish	Material
24566-100	Countersunk Screw	18mm	100	M4		Stainless Steel
24566-104	Panhead Screw	8mm	100	M4		Stainless Steel
24566-103	Panhead Screw	10mm	100	M4		Stainless Steel
24566-102	Panhead Screw	14mm	100	M4		Stainless Steel

Table 2/2

Număr de catalog	Works With	Quick Ship
24566-105	Subracks	No
24560-140	Subracks	No
24566-106	Subracks	No
24566-101	Subracks	No
24566-100	Subracks	No
24566-104	Subracks	No
24566-103	Subracks	No
24566-102	Subracks	No

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE