

Varistar Colocation Cabinet, RAL 9003

Data Solutions



Colocation cabinets with 2, 3 or 4 divider units in RAL 9003 to accommodate servers while separating access and cabling of the compartments.

CERTIFICATIONS



CARACTERÍSTICAS

Colocation cabinets with compartments to accommodate e.g. servers

Flexible cabling, possible from above, below, left or right (data and power cables can be run separately)

Multi-point door locking

Perforated doors

Protection class IP 20

Color RAL 9003

ESPECIFICAÇÕES

Product Type: Rack

Frame Material: Aço

Table 1/3

Número de catálogo	Rack Height	Altura	Cladding Material	Frame Color	Largura	Frame Color Code
--------------------	-------------	--------	-------------------	-------------	---------	------------------

12130-202	40U	2000mm	Aço	Signal White	600mm	RAL 7021
12130-203	39U	2000mm	Aço	Signal White	600mm	RAL 7021
12130-204	40U	2000mm	Aço	Signal White	600mm	RAL 7021
12130-205	40U	2000mm	Aço	Signal White	800mm	RAL 7021
12130-206	39U	2000mm	Aço	Black Grey	800mm	RAL 7021
12130-207	40U	2000mm	Aço	Signal White	800mm	RAL 7021
12130-208	44U	2200mm	Aço	Signal White	600mm	RAL 7021
12130-209	45U	2200mm	Aço	Signal White	600mm	RAL 7021
12130-210	44U	2200mm	Aço	Signal White	600mm	RAL 7021
12130-211	44U	2200mm	Aço	Signal White	800mm	RAL 7021
12130-212	45U	2200mm	Aço	Black Grey	800mm	RAL 7021
12130-213	44U	2200mm	Aço	Signal White	800mm	RAL 7021
12130-214	40U	2000mm	Aço	Signal White	600mm	RAL 7021
12130-215	39U	2000mm	Aço	Signal White	600mm	RAL 7021
12130-216	40U	2000mm	Aço	Signal White	600mm	RAL 7021
12130-217	40U	2000mm	Aço	Signal White	800mm	RAL 7021
12130-218	39U	2000mm	Aço	Black Grey	800mm	RAL 7021
12130-219	40U	2000mm	Aço	Signal White	800mm	RAL 7021
12130-220	44U	2200mm	Aço	Signal White	600mm	RAL 7021

12130-221	45U	2200mm	Aço	Signal White	600mm	RAL 7021
12130-222	44U	2200mm	Aço	Signal White	600mm	RAL 7021
12130-223	44U	2200mm	Aço	Signal White	800mm	RAL 7021
12130-224	45U	2200mm	Aço	Signal White	800mm	RAL 7021
12130-225	44U	2200mm	Aço	Signal White	800mm	RAL 7021
12130-257	45U	2450mm	Aço	Signal White	600mm	RAL 7021
12130-258	48U	2450mm	Aço	Signal White	600mm	RAL 7021
12130-259	48U	2450mm	Aço	Signal White	600mm	RAL 7021
12130-260	45U	2450mm	Aço	Signal White	800mm	RAL 7021
12130-261	48U	2450mm	Aço	Signal White	800mm	RAL 7021
12130-262	48U	2450mm	Aço	Signal White	800mm	RAL 7021
12130-269	45U	2450mm	Aço	Signal White	600mm	RAL 7021
12130-270	48U	2450mm	Aço	Signal White	600mm	RAL 7021
12130-271	48U	2450mm	Aço	Signal White	600mm	RAL 7021
12130-272	45U	2450mm	Aço	Signal White	800mm	RAL 7021
12130-273	48U	2450mm	Aço	Signal White	800mm	RAL 7021
12130-274	48U	2450mm	Aço	Signal White	800mm	RAL 7021

Table 2/3

Número de catálogo	Cladding Color	Cladding Color Code	Profundidade	Quantidade por embalagem	Number of Compartments	Acabamento
--------------------	----------------	---------------------	--------------	--------------------------	------------------------	------------

12130-202	Signal White	RAL 9003	1000mm	1	2	Pintura electrostática com Acabamento Texturado
12130-203	Signal White	RAL 9003	1000mm	1	3	Pintura electrostática com Acabamento Texturado
12130-204	Signal White	RAL 9003	1000mm	1	4	Pintura electrostática com Acabamento Texturado
12130-205	Signal White	RAL 9003	1000mm	1	2	Pintura electrostática com Acabamento Texturado
12130-206	Signal White	RAL 9003	1000mm	1	3	Pintura electrostática com Acabamento Texturado
12130-207	Signal White	RAL 9003	1000mm	1	4	Pintura electrostática com Acabamento Texturado
12130-208	Signal White	RAL 9003	1000mm	1	2	Pintura electrostática com Acabamento Texturado
12130-209	Signal White	RAL 9003	1000mm	1	3	Pintura electrostática com Acabamento Texturado
12130-210	Signal White	RAL 9003	1000mm	1	4	Pintura electrostática com Acabamento Texturado

12130-211	Signal White	RAL 9003	1000mm	1	2	Pintura electrostática com Acabamento Texturado
12130-212	Signal White	RAL 9003	1000mm	1	3	Pintura electrostática com Acabamento Texturado
12130-213	Signal White	RAL 9003	1000mm	1	4	Pintura electrostática com Acabamento Texturado
12130-214	Signal White	RAL 9003	1200mm	1	2	Pintura electrostática com Acabamento Texturado
12130-215	Signal White	RAL 9003	1200mm	1	3	Pintura electrostática com Acabamento Texturado
12130-216	Signal White	RAL 9003	1200mm	1	4	Pintura electrostática com Acabamento Texturado
12130-217	Signal White	RAL 9003	1200mm	1	2	Pintura electrostática com Acabamento Texturado
12130-218	Signal White	RAL 9003	1200mm	1	3	Pintura electrostática com Acabamento Texturado
12130-219	Signal White	RAL 9003	1200mm	1	4	Pintura electrostática com Acabamento Texturado

12130-220	Signal White	RAL 9003	1200mm	1	2	Pintura electrostática com Acabamento Texturado
12130-221	Signal White	RAL 9003	1200mm	1	3	Pintura electrostática com Acabamento Texturado
12130-222	Signal White	RAL 9003	1200mm	1	4	Pintura electrostática com Acabamento Texturado
12130-223	Signal White	RAL 9003	1200mm	1	2	Pintura electrostática com Acabamento Texturado
12130-224	Signal White	RAL 9003	1200mm	1	3	Pintura electrostática com Acabamento Texturado
12130-225	Signal White	RAL 9003	1200mm	1	4	Pintura electrostática com Acabamento Texturado
12130-257	Signal White	RAL 9003	1000mm	1	2	Pintura electrostática com Acabamento Texturado
12130-258	Signal White	RAL 9003	1000mm	1	3	Pintura electrostática com Acabamento Texturado
12130-259	Signal White	RAL 9003	1000mm	1	4	Pintura electrostática com Acabamento Texturado

12130-260	Signal White	RAL 9003	1000mm	1	2	Pintura electrostática com Acabamento Texturado
12130-261	Signal White	RAL 9003	1000mm	1	3	Pintura electrostática com Acabamento Texturado
12130-262	Signal White	RAL 9003	1000mm	1	4	Pintura electrostática com Acabamento Texturado
12130-269	Signal White	RAL 9003	1200mm	1	2	Pintura electrostática com Acabamento Texturado
12130-270	Signal White	RAL 9003	1200mm	1	3	Pintura electrostática com Acabamento Texturado
12130-271	Signal White	RAL 9003	1200mm	1	4	Pintura electrostática com Acabamento Texturado
12130-272	Signal White	RAL 9003	1200mm	1	2	Pintura electrostática com Acabamento Texturado
12130-273	Signal White	RAL 9003	1200mm	1	3	Pintura electrostática com Acabamento Texturado
12130-274	Signal White	RAL 9003	1200mm	1	4	Pintura electrostática com Acabamento Texturado

Table 3/3

Número de catálogo	Material	Static Load
--------------------	----------	-------------

12130-202	Aço	800kg
12130-203	Aço	800kg
12130-204	Aço	800kg
12130-205	Aço	800kg
12130-206	Aço	800kg
12130-207	Aço	800kg
12130-208	Aço	800kg
12130-209	Aço	800kg
12130-210	Aço	800kg
12130-211	Aço	800kg
12130-212	Aço	800kg
12130-213	Aço	800kg
12130-214	Aço	800kg
12130-215	Aço	800kg
12130-216	Aço	800kg
12130-217	Aço	800kg
12130-218	Aço	800kg
12130-219	Aço	800kg
12130-220	Aço	800kg

12130-221	Aço	800kg
12130-222	Aço	800kg
12130-223	Aço	800kg
12130-224	Aço	800kg
12130-225	Aço	800kg
12130-257	Aço	800kg
12130-258	Aço	800kg
12130-259	Aço	800kg
12130-260	Aço	800kg
12130-261	Aço	800kg
12130-262	Aço	800kg
12130-269	Aço	800kg
12130-270	Aço	800kg
12130-271	Aço	800kg
12130-272	Aço	800kg
12130-273	Aço	800kg
12130-274	Aço	800kg

DETALHES ADICIONAIS DO PRODUTO

Side panel must be ordered separately. For suitable cable panel see Accessories.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE