


Universal Busbar Support with Neutral Circuit, High Ampacity



CERTIFICATIONS



CARACTERÍSTICAS

Universal fixing system

Installs quickly and easily

Extremely robust construction

Screws are made from non-magnetic stainless steel

Halogen free insulators

ESPECIFICAÇÕES

Max Working Voltage, IEC (Ui):	1000;1500
Em conformidade com:	IEC® 60439.1;IEC® 61439.1;IEC® 60695-2-11 (Glow Wire Test 960 °C)
Flammability Rating:	UL® 94V-0
Temperatura de trabalho:	-40 to 130 °C


Table 1/2

Número de catálogo	Número do artigo	Material	Typical Application Current Rating	Busbars per Phase	Largura do barramento	Busbar Thickness
UBS1-10TN-160	561500	Aço, Glass Fibre Reinforced Polyamide	3500 A	1	160 mm	10 mm
UBS2-10TN-160	561870	Aço, Glass Fibre Reinforced Polyamide	5700 A	1 - 2	160 mm	10 mm
UBS2-10TN-200	561880	Aço, Glass Fibre Reinforced Polyamide	5700 A	1 - 2	200 mm	10 mm
UBS3-10TN-160	561540	Aço, Glass Fibre Reinforced Polyamide	6200 A	1 - 3	160 mm	10 mm

Table 2/2

Número de catálogo	Número do artigo	Largura (W)	A
UBS1-10TN-160	561500	300 mm	70 mm
UBS2-10TN-160	561870	480 mm	110 mm
UBS2-10TN-200	561880	480 mm	110 mm
UBS3-10TN-160	561540	480 mm	110 mm

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência
técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE