

T-Series Vertical Filler Material Kit



T-Series vertical filler material kits contain the following: Filler material, two vertical packings, pouring basin ceramic guide tube and pouring basin crucible ceramic and disk. All filler material kits contain one-time use components that are sized to a specific sleeve, pouring basin and pouring basin crucible combination. Ordering filler material kits simplifies ordering, reduces order errors and helps ensure proper sizing of components.

CARACTERISTICAS

Simplifies ordering

Used to splice the same diameter bars

All components are for one-time use

ESPECIFICAÇÕES

Table 1/1

Número de catálogo	Sleeve	Tamanho da viga de reforço, metric	Tamanho da viga de reforço, EUA	Tamanho da viga de reforço, Canadá
RBT121018B	Standard Length	38 mm	#12	
RBT4101B	Standard Length	12 mm	#4	10M
RBT5101B	Standard Length	16 mm	#5	15M
RBT6101B	Standard Length	20 mm	#6	20M
RBT7101B	Standard Length	22 mm	#7	
RBT81011B	Extended Length	25 mm	#8	25M
RBT8101B	Standard Length	25 mm	#8	25M

Número de catálogo	Sleeve	Tamanho da viga de reforço, metric	Tamanho da viga de reforço, EUA	Tamanho da viga de reforço, Canadá
RBT91011B	Extended Length	28 mm	#9	30M
RBT9101B	Standard Length	28 mm	#9	30M
RBT10911B	Extended Length	32 mm	#10	
RBT1091B	Standard Length	32 mm	#10	
RBT111011B	Extended Length	36 mm	#11	35M
RBT11101B	Standard Length	36 mm	#11	35M
RBT14101B	Standard Length	43 mm	#14	45M
RBT1891B	Standard Length	57 mm	#18	55M

DETALHES ADICIONAIS DO PRODUTO

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

Filler material kits are a component in splice kits. Care should be taken to avoid duplication of orders.

Components can also be purchased separately: (1) Filler Material, (2) Vertical Top Packing, (3) Vertical Bottom Packing, (4) Pouring Basin Ceramic Guide Tube, and (5) Crucible Ceramic and Disk.

Filler Material Kit Components				
Filler Material Kit	Filler Material	Packing (2 Required)	Pouring Basin Ceramic Insert and Disk	Pouring Basin Ceramic Guide Tube
RBT4101B	RBF40	RBS354710 RBS354710	RBS5037	RBS5039
RBT5101B	RBF40	RBS354710 RBS35475	RBS5037	RBS5038
RBT6101B	RBF50	RBS35473.5 RBS35477	RBS5037	RBS5038
RBT7101B	RBF50	RBS35474 RBS35478	RBS5037	RBS5038
RBT81011B	RBF70	RBS354710 RBS35475	RBS5037	RBS5038
RBT8101B	RBF55	RBS354710 RBS35475	RBS5037	RBS5038
RBT91011B	RBF90	RBS354711 RBS35475.5	RBS5037	RBS5038
RBT9101B	RBF80	RBS354711 RBS35475.5	RBS5037	RBS5038
RBT10911B	RBF105	RBS354712 RBS35476	RBS5037	RBS5038
RBT1091B	RBF90	RBS354712 RBS35476	RBS5037	RBS5038
RBT111011B	RBF125	RBS354712 RBS35476	RBS5037	RBS5038
RBT11101B	RBF105	RBS354712 RBS35476	RBS5037	RBS5038
RBT121018B	RBF180	RBS354715 RBS35477	RBS5037	RBS5038
RBT14101B	RBF195	RBS354715 RBS35477	RBS5037	RBS5039
RBT1891B	RBF270	RBS354720 RBS35479	RBS5037	RBS5039

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência
técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE