

# Varistar CP Swing Frame for 800 mm Width

## Concessionárias de energia

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° / 160° movement and flexible pivot point.

### RECURSOS

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks

120° / 160° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

### ESPECIFICAÇÕES

Table 1/2

| Número do catálogo | Rack Height | Cor        | Color Code | Altura  | Material | Product Type       |
|--------------------|-------------|------------|------------|---------|----------|--------------------|
| 21630-669          | 24 U        | Black Grey | RAL 7021   | 1200 mm | Aço      | Cabinet/Rack Frame |
| 21630-680          | 24 U        | Black Grey | RAL 7021   | 1200 mm | Aço      | Cabinet/Rack Frame |
| 21630-671          | 29 U        | Black Grey | RAL 7021   | 1400 mm | Aço      | Cabinet/Rack Frame |
| 21630-681          | 29 U        | Black Grey | RAL 7021   | 1400 mm | Aço      | Cabinet/Rack Frame |
| 21630-673          | 33 U        | Black Grey | RAL 7021   | 1600 mm | Aço      | Cabinet/Rack Frame |
| 21630-682          | 33 U        | Black Grey | RAL 7021   | 1600 mm | Aço      | Cabinet/Rack Frame |
| 21630-675          | 38 U        | Black Grey | RAL 7021   | 1800 mm | Aço      | Cabinet/Rack Frame |

| Número do catálogo | Rack Height | Cor        | Color Code | Altura  | Material | Product Type       |
|--------------------|-------------|------------|------------|---------|----------|--------------------|
| 21630-683          | 38 U        | Black Grey | RAL 7021   | 1800 mm | Aço      | Cabinet/Rack Frame |
| 21630-677          | 42 U        | Black Grey | RAL 7021   | 2000 mm | Aço      | Cabinet/Rack Frame |
| 21630-684          | 42 U        | Black Grey | RAL 7021   | 2000 mm | Aço      | Cabinet/Rack Frame |
| 21630-679          | 47 U        | Black Grey | RAL 7021   | 2200 mm | Aço      | Cabinet/Rack Frame |
| 21630-685          | 47 U        | Black Grey | RAL 7021   | 2200 mm | Aço      | Cabinet/Rack Frame |

Table 2/2

| Número do catálogo | Protection Rating | Largura |
|--------------------|-------------------|---------|
| 21630-669          | IP20              | 800 mm  |
| 21630-680          | IP20              | 800 mm  |
| 21630-671          | IP20              | 800 mm  |
| 21630-681          | IP20              | 800 mm  |
| 21630-673          | IP20              | 800 mm  |
| 21630-682          | IP20              | 800 mm  |
| 21630-675          | IP20              | 800 mm  |
| 21630-683          | IP20              | 800 mm  |
| 21630-677          | IP20              | 800 mm  |
| 21630-684          | IP20              | 800 mm  |
| 21630-679          | IP20              | 800 mm  |
| 21630-685          | IP20              | 800 mm  |

## ADDITIONAL PRODUCT DETAILS

---

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

## AVISO

---

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**