

TT1000 Water Sensing Cable, Modular



nVent RAYCHEM TraceTek TT1000-XX-PC are a range of fixed length water sensing cables with factory installed plastic connectors. Mainly used in commercial building applications, it is typically intended for leak detection under raised floors, in mechanical rooms and similar flat surface areas. It detects the presence of water at any point along its length. Installed with an alarm and locating module, the cable senses water leaks, triggers an alarm and pinpoints the location.

RECURSOS

Advanced technology: rugged conductive polymer and fluoropolymer construction, resistant to corrosion and abrasion

Simple and fast to install: small, lightweight and flexible

Easy to design, fast drying, and reuseable

Distributed leak detection and location over a wide range of areas

Reliable and durable, 10 year product warranty available

ESPECIFICAÇÕES

Diâmetro externo:	6 mm
Max Operating Temperature:	75 °C
Detection Method:	Raychem Conductive-Polymer Technology
Detection:	Water

Table 1/1

Número do catálogo	Nome do item	Comprimento
017859-000	TT1000-7.5M/25FT-PC	7.5 m
072827-000	TT1000-5M/17FT-PC	5 m
391887-000	TT1000-3M/10FT-PC	3 m
396807-000	TT1000-30M/100FT-PC	30 m

Número do catálogo	Nome do item	Comprimento
409271-000	TT1000-1M/3FT-PC	1 m
805147-000	TT1000-15M/50FT-PC	15 m
P000000702	TT1000-100M/330FT-PC	100 m
P000000864	TT1000-25M/82FT-PC	25 m
P000000873	TT1000-50M/165FT-PC	50 m
P000001222	TT1000-6M/20FT-PC	6 m
P000001223	TT1000-10M/33FT-PC	10 m
P000001224	TT1000-12M/39FT-PC	12 m
P000001225	TT1000-30M/98FT-PC	30 m
P000001226	TT1000-45M/147FT-PC	45 m

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT