

Interscale Flexible Heat Conductor (FHC), 20 mm

NÚMERO DE CATÁLOGO

24830-005



Conductor block expands/contracts vertically to compensate for tolerance stack up and optimizes surface contact and pressure along the thermal path; eliminates the need for a thermal gap pad.

CERTIFICATIONS



CARACTERÍSTICAS

Designed for Intel, AMD, Via, Freescale, NVidia and Texas Instrument processors that employ a BGA socket

Provides industry-leading conduction cooling performance, 10% improvement over current conduction cooling methods

Patent pending conduction cooling solution for small form factor electronics

Secured to PCB with thermally conductive adhesive tape

Conductor block expands/contracts vertically to compensate for tolerance stack up and optimizes surface contact and pressure along the thermal path; eliminates the need for a thermal gap pad

Compatible with Interscale C enclosures

CARATERÍSTICAS DO PRODUTO

Product Type: Conductor Block

Família de produtos: Interscale

Tipo: Heat Conductor

Works With: Cases

Quantidade por embalagem: 1

Profundidade: 22mm

Largura: 22mm

Acabamento: Anodized; Aluminum-Zinc Plated

Gross Weight: 0.074kg

Material: Alumínio; Aço

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE