

EuropacPRO Rugged Rear Angle for Textile EMC Gasket



Corner profile covers the slot between the side panel and the rear panel of a subrack. Needed for a proper EMC shielding.

CERTIFICATIONS



CARACTERÍSTICAS

Required for shielding of rear

Can also be used as front closure when using a depth-adjustable 19" support bracket

ESPECIFICAÇÕES

Material:	Aluminio
Product Type:	Cover
Família de produtos:	EuropacPRO
Tipo:	Rugged
Works With:	Subracks

Table 1/2

Número de catálogo	Rack Height	Design Feature	Quantidade por embalagem	Altura	Unidade de embalagem	Certifications
24566-497	6U	CPCI	2	265.9mm	Pair	

Número de catálogo	Rack Height	Design Feature	Quantidade por embalagem	Altura	Unidade de embalagem	Certifications
24566-197	3U	CPCI	2	132.6mm	Pair	
24566-199	3U		2	132.6mm	Pair	RoHS
24566-499	6U		2	265.9mm	Pair	RoHS

Table 2/2

Número de catálogo	Envio rápido
24566-497	Não
24566-197	Não
24566-199	Não
24566-499	Não

DETALHES ADICIONAIS DO PRODUTO

Please order EMC textile gasket separately.

Corner profile cannot be used together with adapter for rear mounting.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE