

LED Lights for Cabinets



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

CERTIFICATIONS



CARACTERISTICAS

Lights can be easily mounted vertically or horizontally.

Simple through-wiring based on a plug-and-play system.

ESPECIFICAÇÕES

Product Type: Light

Table 1/2

Número de catálogo	Accessory Type	Grau de proteção	Quantidade por embalagem	Cor	Acabamento	Tipo
57274	Lights	IP20	1	Black	Smooth Matte	Cabinet Light, Terminal Block
57275	Lights	IP20	2	Black	Smooth Matte	Cabinet Light, Magnet
57265	Lights	IP20	1	Black	Smooth Matte	Cabinet Light
57272	Lights	IP20	1	Black	Smooth Matte	Connection Cable

Número de catálogo	AccessoryType	Grau de proteção	Quantidade por embalagem	Cor	Acabamento	Tipo
57273	Lights	IP20	1	Black	Smooth Matte	Cabinet Light

Table 2/2			
Número de catálogo	Peso	Certifications	Envio rápido
57274	0.07kg	RoHS	Não
57275	0.08kg	RoHS	Não
57265	0.24kg	RoHS, CE	Não
57272	0.3kg	RoHS	Não
57273	0.3kg	RoHS	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE