


# Varistar Side Separating Wall



Side panel for side by side cabinets replacing 2 individual cabinet side panles. The seperating panel is mounted between to racks and fully compatible with all air blanking panels.

## CERTIFICATIONS



## CARACTERISTICAS

Prevents unauthorized access

For cabinets arranged in rows, wall replaces individual cabinet side walls

## ESPECIFICAÇÕES

**Acabamento:** Aluminum-Zinc Plated

**Product Type:** Cabinet/Rack Panel

**Material:** Aço

Table 1/1

| Número de catálogo | Rack Height | Altura | Profundidade | Quantidade por embalagem | Tipo            | Envio rápido |
|--------------------|-------------|--------|--------------|--------------------------|-----------------|--------------|
| 23130-580          | 52U         | 2450mm | 1000mm       | 1                        | Separating Wall | Não          |

| Número de catálogo | Rack Height | Altura | Profundidade | Quantidade por embalagem | Tipo            | Envio rápido |
|--------------------|-------------|--------|--------------|--------------------------|-----------------|--------------|
| 23130-485          | 47U         | 2200mm | 1200mm       | 1                        | Separating Wall | Não          |
| 23130-480          | 42U         | 2000mm | 1000mm       | 1                        | Separating Wall | Não          |
| 23130-508          | 42U         | 2000mm | 1100mm       | 1                        | Separating Wall | Não          |
| 23130-510          | 52U         | 2450mm | 1100mm       | 1                        | Separating Wall | Não          |
| 23130-481          | 42U         | 2000mm | 1200mm       | 1                        | Separating Wall | Não          |
| 23130-581          | 52U         | 2450mm | 1200mm       | 1                        | Separating Wall | Não          |
| 23130-484          | 47U         | 2200mm | 1000mm       | 1                        | Separating Wall | Não          |
| 23130-509          | 47U         | 2200mm | 1100mm       | 1                        | Separating Wall | Não          |

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



O nosso forte portefólio de marcas:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**