

# Guide Rail With Coding for CompactPCI/ VME64x, PC

## Concessionárias de energia

New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

### RECURSOS

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to a optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

Optional ESD clip for an conductive contact between PCB and horizontal rail available

Storage temperature: from -40 °C ... 130 °C

### ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Material	Cor	Package Quantity	Board Depth	Groove Width	Em conformidade com
24568-356	Policarbonato	Vermelho		160 mm	2	EN 45545-2
24568-357	Policarbonato	Vermelho		70 mm	2	EN 45545-2

<b>Número do catálogo</b>	<b>Material</b>	<b>Cor</b>	<b>Package Quantity</b>	<b>Board Depth</b>	<b>Groove Width</b>	<b>Em conformidade com</b>
24568-358	Policarbonato	Grey		160 mm	2	EN 45545-2
24568-360	Policarbonato	Grey		70 mm	2	EN 45545-2
64568-085	Policarbonato	Vermelho	50	70 mm	2	EN 45545-2
64568-086	Policarbonato	Grey	50	70 mm	2	EN 45545-2
64568-089	Policarbonato	Vermelho	50	160 mm	2	EN 45545-2
64568-090	Policarbonato	Grey	50	160 mm	2	EN 45545-2
64568-091	Policarbonato	Vermelho	50	220 mm	2	EN 45545-2
64568-092	Policarbonato	Grey	50	220 mm	2	EN 45545-2
24568-331	Polycarbonate, Aluminum	Red, Silver	10	280 mm	2,5	EN 45545-2
24568-332	Polycarbonate, Aluminum	Red, Silver	10	340 mm	2,5	EN 45545-2
24568-341	Polycarbonate, Aluminum	Grey, Silver	10	280 mm	2,5	EN 45545-2
24568-342	Polycarbonate, Aluminum	Grey, Silver	10	340 mm	2,5	EN 45545-2
64568-111	Polycarbonate, Aluminum	Red, Silver	50	220 mm	2,5	EN 45545-2
64568-112	Polycarbonate, Aluminum	Grey, Silver	50	220 mm	2,5	EN 45545-2
64568-110	Polycarbonate, Aluminum	Grey, Silver	50	160 mm	2,5	EN 45545-2
64568-109	Polycarbonate, Aluminum	Red, Silver	50	160 mm	2,5	EN 45545-2

Table 2/2

<b>Número do catálogo</b>	<b>Product Family</b>	<b>Product Type</b>	<b>Tipo</b>	<b>Works With</b>
---------------------------	-----------------------	---------------------	-------------	-------------------

24568-356	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-357	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-358	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-360	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-085	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-086	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-089	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-090	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems

64568-091	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-092	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-331	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-332	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-341	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-342	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-111	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-112	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems

64568-110	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-109	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems

## ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**