

Varistar CP Glazed Door With 1-Point Locking

Concessionárias de energia

RECURSOS

St, 1.5 mm

Security glass, 6 mm

Key lock cover

Opening angle 180°

ESPECIFICAÇÕES

Table 1/3

Número do catálogo	Rack Height	Altura	Largura	Locking Type	Cor	Color Code
21630-392	24 U	1200 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-393	24 U	1200 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-481	24 U	1200 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-482	24 U	1200 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-394	29 U	1400 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-395	29 U	1400 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-483	29 U	1400 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-484	29 U	1400 mm	800 mm	Single Point Locking	Black Grey	RAL 7021

Número do catálogo	Rack Height	Altura	Largura	Locking Type	Cor	Color Code
21630-396	33 U	1600 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-397	33 U	1600 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-485	33 U	1600 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-486	33 U	1600 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-398	38 U	1800 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-399	38 U	1800 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-487	38 U	1800 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-488	38 U	1800 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-016	42 U	2000 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-017	42 U	2200 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-489	42 U	2000 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-490	42 U	2000 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-018	47 U	2000 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-019	47 U	2200 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-491	47 U	2200 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-492	47 U	2200 mm	800 mm	Single Point Locking	Black Grey	RAL 7021

Table 2/3

Número do catálogo	Em conformidade com	Acabamento	Material	Product Type	Protection Rating	Tipo
--------------------	---------------------	------------	----------	--------------	-------------------	------

21630-392	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-393	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-481	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-482	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-394	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-395	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-483	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-484	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-396	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-397	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-485	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-486	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-398	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-399	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-487	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-488	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-016	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-017	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-489	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door

21630-490	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-018	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-019	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-491	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-492	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door

Table 3/3

Número do catálogo	Works With
21630-392	Varistar CP
21630-393	Varistar CP
21630-481	Varistar CP
21630-482	Varistar CP
21630-394	Varistar CP
21630-395	Varistar CP
21630-483	Varistar CP
21630-484	Varistar CP
21630-396	Varistar CP
21630-397	Varistar CP
21630-485	Varistar CP
21630-486	Varistar CP
21630-398	Varistar CP

Número do catálogo	Works With
21630-399	Varistar CP
21630-487	Varistar CP
21630-488	Varistar CP
21630-016	Varistar CP
21630-017	Varistar CP
21630-489	Varistar CP
21630-490	Varistar CP
21630-018	Varistar CP
21630-019	Varistar CP
21630-491	Varistar CP
21630-492	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE