

Varistar CP Plain Steel Door, Seismic EMC and IP55, Multi-Point Locking

Power Utilities

EMC and IP55 Steel Door with lever handle and 4-Point locking.

CARACTERISTICAS

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for Seismic & EMC applications

ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Rack Height	Altura	Largura	Cor	Código de cor	Em conformidade com
21630-760	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-761	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-762	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-763	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529

Número de catálogo	Rack Height	Altura	Largura	Cor	Código de cor	Em conformidade com
21630-764	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-765	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-766	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-767	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529

Table 2/2

Número de catálogo	Locking Type	Material	Product Type	Grau de proteção	Tipo	Works With
21630-760	4-Point Locking	Aço	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-761	4-Point Locking	Aço	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-762	4-Point Locking	Aço	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-763	4-Point Locking	Aço	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-764	4-Point Locking	Aço	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-765	4-Point Locking	Aço	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-766	5-Point Locking	Aço	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-767	5-Point Locking	Aço	Cabinet Door	IP55	Steel Door, Plain	Varistar CP

DETALHES ADICIONAIS DO PRODUTO

Please purchase the grounding kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE