

Varistar CP Seismic Base/Plinth

Concessionárias de energia

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

RECURSOS

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Largura	Profundidade	Cor	Color Code	Em conformidade com	Altura
21630-110	600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-111	600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-112	600 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-113	600 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-114	800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-115	800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm

Número do catálogo	Largura	Profundidade	Cor	Color Code	Em conformidade com	Altura
21630-117	800 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-116	800 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	800 mm

Table 2/2					
Número do catálogo	Material	Product Type	Carga estática	Tipo	Works With
21630-110	Aço	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-111	Aço	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-112	Aço	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-113	Aço	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-114	Aço	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-115	Aço	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-117	Aço	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-116	Aço	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE