


# Low-Profile Splice Kit



nVent RAYCHEM S-150 is a cold-applied low profile splice for trace heating cables in both non-hazardous and hazardous locations. Includes cold-applied heating cable core sealer.

## RECURSOS

Simple and fast to install and test

Cold-applied: no heat gun or hot work permit required, re-enterable

High performance: resistant to impact, high temperature, chemicals and UV

Reliable during long life: 10 year product warranty available, maintenance free

## ESPECIFICAÇÕES

Table 1/2

| Número do catálogo | Nome do item | Model                       | Tipo de conexão | Voltage Rating for FM, CSA | Voltage Rating for PTB | Current Rating for FM, CSA |
|--------------------|--------------|-----------------------------|-----------------|----------------------------|------------------------|----------------------------|
| 497537-000         | S-150        | Heating Cable/Heating Cable | Cold Applied    | 277 V                      | 254 V                  | 50 A                       |

Table 2/2

| Número do catálogo | Nome do item | Current Rating for PTB | Max Exposure Temperature | Below Insulation |
|--------------------|--------------|------------------------|--------------------------|------------------|
| 497537-000         | S-150        | 40 A                   | 215 °C                   | Sim              |

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos

à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

**América do Norte**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East,  
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**América Latina**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**