

PXI Express Controller, 4 TE, W-11865MLE 32-1024

NÚMERO DE CATÁLOGO

21265-170



The nVent SCHROFF PXIe embedded controller is the most compact and powerful 3 U/4 HP embedded controller for PXI Express and CPClexp platforms. With its comprehensive and future-proof interface and compute power capabilities, it is ideally suitable for test and measurement applications. The controller is driven by a 11th generation Intel® Xeon® processor, combined with up to 64 GB DDR4 memory and supports high bandwidth applications with PCIe Gen4 and 10GBASE-T interconnectivity.

CARACTERÍSTICAS

PXI Express Systemcontroller, 3 HE, 4 TE, mit Intel-Prozessor W-11865MLE

PXI™-5 PXI Express hardware spec. Rev.2.0 compliant

Maximum 28 GB/s PCIe Bandwidth

Upgradeable m.2 and DDR4 Storage

2x USB3.1, 2x 10 GbE and 1x DP 1.2 on the front panel

Full customizable AMI Aptio® Embedded BIOS

CARATERÍSTICAS DO PRODUTO

Product Type: System

Tipo: Controller

Data Transfer: PCIe Gen3

Rack Height: 3U

Em conformidade com: PXISA PXI-5 R1.1

Profundidade: 160mm

Gross Weight: 0.562kg

Quantidade por embalagem: 1

DETALHES ADICIONAIS DO PRODUTO

Conform to PICMG rev. 3.0 and PXI-7.

Modified Controllers available on request.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE