


панель электропитания, UTE

Data Solutions



Компактная модульная конструкция панели электропитания с множеством функциональных элементов. Распределительный блок питания с алюминиевым шасси размером 1 U x 1 U легко интегрируется в шкаф с розетками UTE.

CERTIFICATIONS



FEATURES

230 В., 16 А

В соответствии с NFC 61-303

Панель электропитания с розетками UTE

Монтажная высота 1 U

Возможен горизонтальный и вертикальный монтаж

Сетевой кабель 2 м, штекер SCHUKO/UTE

При установке панель электропитания можно развернуть в любую сторону (с шагом 90°)

SPECIFICATIONS

Material:	Алюминий; Polyamide
Color:	Серый
Product Type:	Панели электропитания

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-220	UTE	4	Нет	230V		1
60110-221	UTE	9	Нет	230V		1
60110-267	UTE	6	Нет	230V	Transient Protection, Mains Suppression Filter	1
60110-225	UTE	8	Да	230V		1
60110-227	UTE	8	Нет	230V	Transient Protection	1
60110-229	UTE	7	Нет	230V	Mains Suppression Filter	1
60110-226	UTE	12	Да	230V		1
60110-222	UTE	12	Нет	230V		1
60110-223	UTE	15	Нет	230V		1
60110-224	UTE	19	Нет	230V		1
60110-231	UTE	6	Нет	230V	Fault Current Protection, Overcurrent Protection	1
60110-228	UTE	6	Нет	230V	Overcurrent Protection	1
60110-230	UTE	6	Нет	230V	Fault Current Protection	1

Table 2/2

Catalog Number	Глубина мм	Finish	Длина мм
60110-220	44mm	Anodized	210mm
60110-221	44mm	Anodized	438.5mm

Catalog Number	Глубина мм	Finish	Длина мм
60110-267	44mm	Anodized	438.5mm
60110-225	44mm	Anodized	438.5mm
60110-227	44mm	Anodized	438.5mm
60110-229	44mm	Anodized	438.5mm
60110-226	44mm	Anodized	947.5mm
60110-222	44mm	Anodized	947.5mm
60110-223	44mm	Anodized	1202mm
60110-224	44mm	Anodized	1753mm
60110-231	88mm	Anodized	438.5mm
60110-228	75mm	Anodized	438.5mm
60110-230	88mm	Anodized	438.5mm

ADDITIONAL PRODUCT DETAILS

Кронштейн для вертикального монтажа заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE