

Шкаф Varistar для совместного размещения оборудования, RAL 7021

Data Solutions



Шкафы для совместного размещения оборудования с 2, 3 или 4 отсеками в цвете RAL 7021 для установки серверов с возможностью разделения доступа и организации кабелей.

CERTIFICATIONS



FEATURES

Шкафы для совместного размещения оборудования с отсеками

Гибкая разводка кабелей, возможна сверху, снизу, слева или справа (кабели передачи данных и питания можно прокладывать отдельно)

Многоточечный замок

Перфорированные двери

Степень защиты IP 20

Цвет RAL 7021 (черно-серый)

SPECIFICATIONS

Product Type: Rack

Frame Material: Сталь

Table 1/3

Catalog Number	Rack Height	Высота мм	Cladding Material	Frame Color	Ширина мм	Frame Color Code
10130-202	40U	2000mm	Сталь	Black Grey	600mm	RAL 7021
10130-203	39U	2000mm	Сталь	Black Grey	600mm	RAL 7021
10130-204	40U	2000mm	Сталь	Black Grey	600mm	RAL 7021
10130-205	40U	2000mm	Сталь	Black Grey	800mm	RAL 7021
10130-206	39U	2000mm	Сталь	Black Grey	800mm	RAL 7021
10130-207	40U	2000mm	Сталь	Black Grey	800mm	RAL 7021
10130-208	44U	2200mm	Сталь	Black Grey	600mm	RAL 7021
10130-209	45U	2200mm	Сталь	Black Grey	600mm	RAL 7021
10130-210	44U	2200mm	Сталь	Black Grey	600mm	RAL 7021
10130-211	44U	2200mm	Сталь	Black Grey	800mm	RAL 7021
10130-212	45U	2200mm	Сталь	Black Grey	800mm	RAL 7021
10130-213	44U	2200mm	Сталь	Black Grey	800mm	RAL 7021
10130-214	40U	2000mm	Сталь	Black Grey	600mm	RAL 7021
10130-215	39U	2000mm	Сталь	Black Grey	600mm	RAL 7021
10130-216	40U	2000mm	Сталь	Black Grey	600mm	RAL 7021
10130-217	40U	2000mm	Сталь	Black Grey	800mm	RAL 7021
10130-218	39U	2000mm	Сталь	Black Grey	800mm	RAL 7021
10130-219	40U	2000mm	Сталь	Black Grey	800mm	RAL 7021

CatalogNumber	Rack Height	Высота мм	Cladding Material	Frame Color	Ширина мм	Frame Color Code
10130-220	44U	2200mm	Сталь	Black Grey	600mm	RAL 7021
10130-221	45U	2200mm	Сталь	Black Grey	600mm	RAL 7021
10130-222	44U	2200mm	Сталь	Black Grey	600mm	RAL 7021
10130-223	44U	2200mm	Сталь	Black Grey	800mm	RAL 7021
10130-224	45U	2200mm	Сталь	Black Grey	800mm	RAL 7021
10130-225	44U	2200mm	Сталь	Black Grey	800mm	RAL 7021
10130-257	45U	2450mm	Сталь	Black Grey	600mm	RAL 7021
10130-258	48U	2450mm	Сталь	Black Grey	600mm	RAL 7021
10130-259	48U	2450mm	Сталь	Black Grey	600mm	RAL 7021
10130-260	45U	2450mm	Сталь	Black Grey	800mm	RAL 7021
10130-261	48U	2450mm	Сталь	Black Grey	800mm	RAL 7021
10130-262	48U	2450mm	Сталь	Black Grey	800mm	RAL 7021
10130-269	45U	2450mm	Сталь	Black Grey	600mm	RAL 7021
10130-270	48U	2450mm	Сталь	Black Grey	600mm	RAL 7021
10130-271	48U	2450mm	Сталь	Black Grey	600mm	RAL 7021
10130-272	45U	2450mm	Сталь	Black Grey	800mm	RAL 7021
10130-273	48U	2450mm	Сталь	Black Grey	800mm	RAL 7021
10130-274	48U	2450mm	Сталь	Black Grey	800mm	RAL 7021

Table 2/3

Catalog Number	Cladding Color	Cladding Color Code	Глубина мм	Package Quantity	Number of Compartments	Finish
10130-202	Black Grey	RAL 7021	1000mm	1	2	Powder Coated
10130-203	Black Grey	RAL 7021	1000mm	1	3	Powder Coated
10130-204	Black Grey	RAL 7021	1000mm	1	4	Powder Coated
10130-205	Black Grey	RAL 7021	1000mm	1	2	Powder Coated
10130-206	Black Grey	RAL 7021	1000mm	1	3	Powder Coated
10130-207	Black Grey	RAL 7021	1000mm	1	4	Powder Coated
10130-208	Black Grey	RAL 7021	1000mm	1	2	Powder Coated
10130-209	Black Grey	RAL 7021	1000mm	1	3	Powder Coated
10130-210	Black Grey	RAL 7021	1000mm	1	4	Powder Coated
10130-211	Black Grey	RAL 7021	1000mm	1	2	Powder Coated
10130-212	Black Grey	RAL 7021	1000mm	1	3	Powder Coated
10130-213	Black Grey	RAL 7021	1000mm	1	4	Powder Coated
10130-214	Black Grey	RAL 7021	1200mm	1	2	Powder Coated
10130-215	Black Grey	RAL 7021	1200mm	1	3	Powder Coated
10130-216	Black Grey	RAL 7021	1200mm	1	4	Powder Coated
10130-217	Black Grey	RAL 7021	1200mm	1	2	Powder Coated
10130-218	Black Grey	RAL 7021	1200mm	1	3	Powder Coated
10130-219	Black Grey	RAL 7021	1200mm	1	4	Powder Coated

CatalogNumber	Cladding Color	Cladding Color Code	Глубина мм	Package Quantity	Number of Compartments	Finish
10130-220	Black Grey	RAL 7021	1200mm	1	2	Powder Coated
10130-221	Black Grey	RAL 7021	1200mm	1	3	Powder Coated
10130-222	Black Grey	RAL 7021	1200mm	1	4	Powder Coated
10130-223	Black Grey	RAL 7021	1200mm	1	2	Powder Coated
10130-224	Black Grey	RAL 7021	1200mm	1	3	Powder Coated
10130-225	Black Grey	RAL 7021	1200mm	1	4	Powder Coated
10130-257	Black Grey	RAL 7021	1000mm	1	2	Powder Coated
10130-258	Black Grey	RAL 7021	1000mm	1	3	Powder Coated
10130-259	Black Grey	RAL 7021	1000mm	1	4	Powder Coated
10130-260	Black Grey	RAL 7021	1000mm	1	2	Powder Coated
10130-261	Black Grey	RAL 7021	1000mm	1	3	Powder Coated
10130-262	Black Grey	RAL 7021	1000mm	1	4	Powder Coated
10130-269	Black Grey	RAL 7021	1200mm	1	2	Powder Coated
10130-270	Black Grey	RAL 7021	1200mm	1	3	Powder Coated
10130-271	Black Grey	RAL 7021	1200mm	1	4	Powder Coated
10130-272	Black Grey	RAL 7021	1200mm	1	2	Powder Coated
10130-273	Black Grey	RAL 7021	1200mm	1	3	Powder Coated
10130-274	Black Grey	RAL 7021	1200mm	1	4	Powder Coated

Table 3/3

Catalog Number	Material	Static Load
10130-202	Сталь	800kg
10130-203	Сталь	800kg
10130-204	Сталь	800kg
10130-205	Сталь	800kg
10130-206	Сталь	800kg
10130-207	Сталь	800kg
10130-208	Сталь	800kg
10130-209	Сталь	800kg
10130-210	Сталь	800kg
10130-211	Сталь	800kg
10130-212	Сталь	800kg
10130-213	Сталь	800kg
10130-214	Сталь	800kg
10130-215	Сталь	800kg
10130-216	Сталь	800kg
10130-217	Сталь	800kg
10130-218	Сталь	800kg
10130-219	Сталь	800kg

Catalog Number	Material	Static Load
10130-220	Сталь	800kg
10130-221	Сталь	800kg
10130-222	Сталь	800kg
10130-223	Сталь	800kg
10130-224	Сталь	800kg
10130-225	Сталь	800kg
10130-257	Сталь	800kg
10130-258	Сталь	800kg
10130-259	Сталь	800kg
10130-260	Сталь	800kg
10130-261	Сталь	800kg
10130-262	Сталь	800kg
10130-269	Сталь	800kg
10130-270	Сталь	800kg
10130-271	Сталь	800kg
10130-272	Сталь	800kg
10130-273	Сталь	800kg
10130-274	Сталь	800kg

ADDITIONAL PRODUCT DETAILS

Боковая панель заказывается отдельно. Информацию о подходящей кабельной панели см. в разделе «Принадлежности».

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE