

Крышка с плоским верхом Varistar CP закрыта

Data Solutions



Плоская верхняя крышка для шкафов Varistar CP, без зон ввода кабелей.

FEATURES

Плоская верхняя крышка, закрытая

SPECIFICATIONS

Product Type: Cabinet/Rack Top Cover

Color Code:RAL 7021Material:Сталь

Table 1/2						
Catalog Number	Ширина мм	Глубина мм	Protection Rating	Package Quantity	Color	Finish
21630-128	600mm	1000mm	IP20	1	Black Grey	Powder Coated
21630-129	600mm	1100mm	IP20	1	Black Grey	Powder Coated
21630-130	600mm	1200mm	IP20	1	Black Grey	Powder Coated
21630-131	800mm	1000mm	IP20	1	Black Grey	Powder Coated

CatalogNumber	Ширина мм	Глубина мм	Protection Rating	Package Quantity	Color	Finish
21630-132	800mm	1100mm	IP20	1	Black Grey	Powder Coated
21630-133	800mm	1200mm	IP20	1	Black Grey	Powder Coated
21630-186	600mm	600mm		1	Black Grey	Powder Coated
21630-187	600mm	800mm		1	Black Grey	Powder Coated
21630-188	600mm	900mm		1	Black Grey	Powder Coated
21630-189	600mm	1000mm		1	Black Grey	Powder Coated
21630-190	600mm	1100mm		1	Black Grey	Powder Coated
21630-191	600mm	1200mm		1	Black Grey	Powder Coated
21630-192	800mm	600mm		1	Black Grey	Powder Coated
21630-193	800mm	800mm		1	Black Grey	Powder Coated
21630-194	800mm	900mm		1	Black Grey	Powder Coated
21630-195	800mm	1000mm		1	Black Grey	Powder Coated
21630-196	800mm	1100mm		1	Black Grey	Powder Coated
21630-197	800mm	1200mm		1	Black Grey	Powder Coated
21630-254	600mm	600mm	IP20	1	Black Grey	Powder Coated
21630-255	600mm	800mm	IP20	1	Black Grey	Powder Coated
21630-256	600mm	900mm	IP20	1	Black Grey	Powder Coated
21630-257	800mm	600mm	IP20	1	Black Grey	Powder Coated

CatalogNumber	Ширина мм	Глубина мм	Protection Rating	Package Quantity	Color	Finish
21630-258	800mm	800mm	IP20	1	Black Grey	Powder Coated
21630-259	800mm	900mm	IP20	1	Black Grey	Powder Coated
21630-260	600mm	300mm	IP20	1	Black Grey	Powder Coated
21630-315	600mm	300mm		1	Black Grey	Powder Coated
21630-557	600mm	300mm	IP55	1	Black Grey	Powder Coated
21630-558	600mm	600mm	IP55	1	Black Grey	Powder Coated
21630-559	600mm	800mm	IP55	1	Black Grey	Powder Coated
21630-560	600mm	900mm	IP55	1	Black Grey	Powder Coated
21630-561	600mm	1000mm	IP55	1	Black Grey	Powder Coated
21630-562	600mm	1100mm	IP55	1	Black Grey	Powder Coated
21630-563	600mm	1200mm	IP55	1	Black Grey	Powder Coated
21630-564	800mm	600mm	IP55	1	Black Grey	Powder Coated
21630-565	800mm	800mm	IP55	1	Black Grey	Powder Coated
21630-566	800mm	900mm	IP55	1	Black Grey	Powder Coated
21630-567	800mm	1000mm	IP55	1	Black Grey	Powder Coated
21630-568	800mm	1100mm	IP55	1	Black Grey	Powder Coated
21630-569	800mm	1200mm	IP55	1	Black Grey	Powder Coated
21630-570	600mm	300mm		1	Black Grey	Powder Coated

CatalogNumber	Ширина мм	Глубина мм	Protection Rating	Package Quantity	Color	Finish
21630-571	600mm	600mm		1	Black Grey	Powder Coated
21630-572	600mm	800mm		1	Black Grey	Powder Coated
21630-573	600mm	900mm		1	Black Grey	Powder Coated
21630-574	600mm	1000mm		1	Black Grey	Powder Coated
21630-575	600mm	1100mm		1	Black Grey	Powder Coated
21630-576	600mm	1200mm		1	Black Grey	Powder Coated
21630-577	800mm	600mm		1	Black Grey	Powder Coated
21630-578	800mm	800mm		1	Black Grey	Powder Coated
21630-579	800mm	900mm		1	Black Grey	Powder Coated
21630-580	800mm	1000mm		1	Black Grey	Powder Coated
21630-581	800mm	1100mm		1	Black Grey	Powder Coated
21630-582	800mm	1200mm		1	Black Grey	Powder Coated

Table 2/2				
Catalog Number	Туре	Works With		
21630-128	Closed	Varistar CP		
21630-129	Closed	Varistar CP		
21630-130	Closed	Varistar CP		
21630-131	Closed	Varistar CP		
21630-132	Closed	Varistar CP		

Catalog Number	Туре	Works With
21630-133	Closed	Varistar CP
21630-186	Closed	Varistar CP
21630-187	Closed	Varistar CP
21630-188	Closed	Varistar CP
21630-189	Closed	Varistar CP
21630-190	Closed	Varistar CP
21630-191	Closed	Varistar CP
21630-192	Closed	Varistar CP
21630-193	Closed	Varistar CP
21630-194	Closed	Varistar CP
21630-195	Closed	Varistar CP
21630-196	Closed	Varistar CP
21630-197	Closed	Varistar CP
21630-254	Closed	Varistar CP
21630-255	Closed	Varistar CP
21630-256	Closed	Varistar CP
21630-257	Closed	Varistar CP
21630-258	Closed	Varistar CP

Catalog Number	Туре	Works With
21630-259	Closed	Varistar CP
21630-260	Closed	Varistar CP
21630-315	Closed	Varistar CP
21630-557	Closed	Varistar CP
21630-558	Closed	Varistar CP
21630-559	Closed	Varistar CP
21630-560	Closed	Varistar CP
21630-561	Closed	Varistar CP
21630-562	Closed	Varistar CP
21630-563	Closed	Varistar CP
21630-564	Closed	Varistar CP
21630-565	Closed	Varistar CP
21630-566	Closed	Varistar CP
21630-567	Closed	Varistar CP
21630-568	Closed	Varistar CP
21630-569	Closed	Varistar CP
21630-570	Closed	Varistar CP
21630-571	С перфорацией	Varistar CP

Catalog Number	Туре	Works With
21630-572	Closed	Varistar CP
21630-573	Closed	Varistar CP
21630-574	Closed	Varistar CP
21630-575	Closed	Varistar CP
21630-576	Closed	Varistar CP
21630-577	Closed	Varistar CP
21630-578	Closed	Varistar CP
21630-579	Closed	Varistar CP
21630-580	Closed	Varistar CP
21630-581	Closed	Varistar CP
21630-582	С перфорацией	Varistar CP

ADDITIONAL PRODUCT DETAILS

Комплект заземления можно приобрести отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE