

Compression Coupler for Copper-Bonded Ground Rod, Pointed



CERTIFICATIONS



CARACTERISTICI

Threadless compression coupler for use with pointed copper-bonded ground rods

Inside of coupler is tapered so ground rod compresses during installation to form an irreversible conductive connection

SPECIFICAȚII

Table 1/2

Număr de catalog	Article Number	Material	Ground Rod Diameter, Nominal	Length (L)	Unit Weight	Complies With
BR12	156650	Brass	1/2"	70mm	0.13 kg	
CC12F	158000	Silicon Bronze	1/2"	69.8mm	0.13 kg	
CC58	158010	Silicon Bronze	5/8"	69.8mm	0.15 kg	IEC® EN 62561-2

Număr de catalog	Article Number	Material	Ground Rod Diameter, Nominal	Length (L)	Unit Weight	Complies With
CC34	158020	Silicon Bronze	3/4"	69.8mm	0.2 kg	IEC® EN 62561-2


Table 2/2

Număr de catalog	Article Number	Certifications
BR12	156650	
CC12F	158000	UL, CSA-US, cUL, CSA
CC58	158010	UL, CSA, cUL, CSA-US, RUS
CC34	158020	CSA, UL, cUL, CSA-US

DETALII SUPLIMENTARE DESPRE PRODUS

IEC® EN 62561-2 supercedes EN 50164-2.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE