

Cadru pentru plăci de acoperire individuale, UFCP-I



Acest cadru din poliester poate fi personalizat cu plastroane plate sau cu fante, oferind o soluție flexibilă atât pentru componentele modulare, cât și pentru cele nemodulare.

CARACTERISTICI

Descriere: Cadrul urmează să fie acoperit cu plăci de acoperire individuale UICP. Pentru cofretele cu lățimea de 600 și 800 mm este prevăzut cu 2 coloane. Distanța dintre UFCP și ușa dulapului: 39 mm; 49 mm pentru UCP750 și modele mai mari. Poziție de montare reversibilă, pentru a crește distanța dintre UFCP și ușa dulapului cu 30 mm.

Material: Poliester.

Finisaj: RAL 7035.

Livrare: Cadru, suporturi, închizătoare cu rotire un sfert de tură și accesorii de montare.

Polyester frame for compact polyester wall mounted enclosure cover plates

The frame can be customized with plain or slotted cover plates to meet customer specific requirements

The frame provides a flexible solution to customers as it can be adapted especially for their components using both plain and slotted cover plates

Both modular and non-modular components can be installed into the same enclosure

Plain or slotted cover plates UICP, are required to be mounted onto the polyester frame

Single frame: UFCP4302, UFCP5402, UFCP6402, UFCP7502

Double frame: UFCP8602, UFCP1082

SPECIFICAȚII

Color: Light Gray
Material: Polyester
Color Code: RAL 7035
Finish: Smooth

Table 1/1						
Număr de catalog	Height	Width	Frame Type	Number of Base Plates Included	Enclosure Material	Quick Ship
UFCP4302	415mm	315mm	Single-Bay	2	Polyester	No
UFCP6402	615mm	415mm	Single-Bay	3	Polyester	No
UFCP5402	515mm	415mm	Single-Bay	3	Polyester	No
UFCP7502	735mm	535mm	Single-Bay	4	Polyester	No
UFCP8602	835mm	635mm	Double-Bay	8	Polyester	No
UFCP1082	1035mm	835mm	Double-Bay	10	Polyester	No

DETALII SUPLIMENTARE DESPRE PRODUS

F.1= unic; F.2= dublu.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE