

Acoperiș ventilat | Dulapuri industriale, CVR



Placa de ventilație pentru acoperiș asigură o ventilație naturală ieftină, oferind în același timp protecție împotriva insectelor și împotriva prafului.

CARACTERISTICI

Descriere: Acoperiș ridicat cu degajări de ventilare de 2,5 mm și filtru.

Material: Placă din oțel de 1,5 mm. Filtru: EU 4 conform cu DIN 24185.

Finisaj: Vopsea pudră structurată, RAL 7035.

Temperatură de rezistență: 100°C.

Protecție: Conform IP 31 | TYPE 1.

Cantitate pachet: 1 bucată cu suporturi de montare și filtru de ventilație.

Notă: Ridică înălțimea dulapului cu 40 mm.

SPECIFICAȚII

Thickness: 1.5mm
Color: Light Gray
Material: Oțel Zincat
Finish: Vopsit Pulbere
Color Code: RAL 7035

Table 1/1						
Număr de catalog	Height	Width	Depth	Product Family	Enclosure Material	Quick Ship
CVR0505R5	58mm	500mm	500mm	Free-Standing	Oțel Zincat	No
CVR0603R5	58mm	600mm	300mm	Free-Standing	Oțel Zincat	No
CVR0604R5	58mm	600mm	400mm	Free-Standing	Oțel Zincat	No
CVR0605R5	58mm	600mm	500mm	Free-Standing	Oțel Zincat	No
CVR0606R5	58mm	600mm	600mm	Free-Standing	Oțel Zincat	No
CVR0608R5	58mm	600mm	800mm	Free-Standing	Oțel Zincat	No
CVR0803R5	58mm	800mm	300mm	Free-Standing	Oțel Zincat	No
CVR0804R5	58mm	800mm	400mm	Free-Standing	Oțel Zincat	No
CVR0805R5	58mm	800mm	500mm	Free-Standing	Oțel Zincat	No
CVR0806R5	58mm	800mm	600mm	Free-Standing	Oțel Zincat	No
CVR0808R5	58mm	800mm	800mm	Free-Standing	Oțel Zincat	No
CVR0809R5	58mm	800mm	900mm	Free-Standing	Oțel Zincat	No
CVR1003R5	58mm	1000mm	300mm	Free-Standing	Oțel Zincat	No
CVR1004R5	58mm	1000mm	400mm	Free-Standing	Oțel Zincat	No
CVR1005R5	58mm	1000mm	500mm	Free-Standing	Oțel Zincat	No
CVR1006R5	58mm	1000mm	600mm	Free-Standing	Oțel Zincat	No

Număr de catalog	Height	Width	Depth	Product Family	EnclosureMaterial	Quick Ship
CVR1008R5	58mm	1000mm	800mm	Free-Standing	Oțel Zincat	No
CVR1203R5	58mm	1200mm	300mm	Free-Standing	Oțel Zincat	No
CVR1204R5	58mm	1200mm	400mm	Free-Standing	Oțel Zincat	No
CVR1205R5	58mm	1200mm	500mm	Free-Standing	Oțel Zincat	No
CVR1206R5	58mm	1200mm	600mm	Free-Standing	Oțel Zincat	No
CVR1208R5	58mm	1200mm	800mm	Free-Standing	Oțel Zincat	No
CVR1604R5	58mm	1600mm	400mm	Free-Standing	Oțel Zincat	No
CVR1605R5	58mm	1600mm	500mm	Free-Standing	Oțel Zincat	No
CVR1606R5	58mm	1600mm	600mm	Free-Standing	Oțel Zincat	No

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE