

# Aisle Containment Closing Bracket

Blanking panels for different aisle containment heights to avoid air leakage at aisle doors.

## CARACTERISTICI

Sheet metal blanking panel

For different aisle heights

## SPECIFICAȚII

**Product Type:** Bracket

**Material:** Oțel

Table 1/2

| Număr de catalog | Height | Package Quantity | Color      | Color Code | Finish         | Type      |
|------------------|--------|------------------|------------|------------|----------------|-----------|
| 21130-782        | 305mm  | 1                | Black Grey | RAL 7021   | Vopsit Pulbere | Air Panel |
| 21130-784        | 470mm  | 1                | Black Grey | RAL 7021   | Vopsit Pulbere | Air Panel |
| 21130-783        | 385mm  | 1                | Black Grey | RAL 7021   | Vopsit Pulbere | Air Panel |

Table 2/2

| Număr de catalog | Width  | Works With        | Quick Ship |
|------------------|--------|-------------------|------------|
| 21130-782        | 1300mm | Aisle Containment | No         |
| 21130-784        | 1300mm | Aisle Containment | No         |
| 21130-783        | 1300mm | Aisle Containment | No         |

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O

instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**