


Backplane With Through-Connected Signal Lines

Backplane with Through Connected Signal Lines.



CERTIFICATIONS



CARACTERISTICI

Power supply at each connector position (row 1 + 32)

Adaptation fields for power connections on 2-layer backplanes

SPECIFICAȚII

Table 1/2

Număr de catalog	Product Type	Number of Slots	Rack Height	Backplane Type	Slot Width	Connector Type
23007-188	Backplane	28	3U	60 Signal Lines	3HP	
23007-010	Backplane	10	3U	60 Signal Lines	4HP	C64F
23007-081	Backplane	21	3U	60 Signal Lines	4HP	
23007-114	Backplane	14	3U	60 Signal Lines	3HP	C64F

Număr de catalog	Product Type	Number of Slots	Rack Height	Backplane Type	Slot Width	Connector Type
23007-040	Backplane	10	3U	60 Signal Lines	4HP	C96F
23007-410	Backplane	10	3U	90 Signal Lines	4HP	C96F
23007-021	Backplane	21	3U	60 Signal Lines	4HP	C64F
23007-421	Backplane	21	3U	90 Signal Lines	4HP	C96F
23007-051	Backplane	21	3U	60 Signal Lines	4HP	C96F
23007-128	Backplane	28	3U	60 Signal Lines	3HP	C64F
23007-158	Backplane	28	3U	60 Signal Lines	3HP	C96F

Table 2/2

Număr de catalog	Power Connector Type	Package Quantity	Quick Ship
23007-188	Fastons 6.3 x 0.8 mm	1	No
23007-010	Fastons 6.3 x 0.8 mm	1	No
23007-081	Fastons 6.3 x 0.8 mm	1	No
23007-114	Fastons 6.3 x 0.8 mm	1	No
23007-040	Fastons 6.3 x 0.8 mm	1	No
23007-410	Fastons 6.3 x 0.8 mm	1	No
23007-021	Fastons 6.3 x 0.8 mm	1	No
23007-421	Fastons 6.3 x 0.8 mm	1	No
23007-051	Fastons 6.3 x 0.8 mm	1	No
23007-128	Fastons 6.3 x 0.8 mm	1	No

Număr de catalog	Power Connector Type	Package Quantity	Quick Ship
23007-158	Fastons 6.3 x 0.8 mm	1	No

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE