

19-дюймовая передняя панель, с отверстиями

Передние панели с вентиляционными отверстиями обеспечивают отвод тепла через отверстия.



CERTIFICATIONS



FEATURES

Передние панели (алюминиевые) с вентиляционными отверстиями обеспечивают отвод тепла

SPECIFICATIONS

Rack Width: 95HP

Material: Алюминий

Аксессуар Тип: Передняя панель **Product Type:** Передняя панель

Table 1/3						
Catalog Number	Rack Height	Finish	Mounting	Package Quantity	Front Finish	Rear Finish
30118-962	1U	Powder Coated	Screw-on Front	1	Painted	Painted
30702-044	1U	Anodized	Screw-on Front	1	Raw	Conductive

CatalogNumber	Rack Height	Finish	Mounting	Package Quantity	Front Finish	Rear Finish
30702-047	1U	Anodized	Screw-on Front	1	Anodized	Anodized
30702-056	1U	Powder Coated	Screw-on Front	1	Painted	Painted
30118-963	2U	Anodized	Screw-on Front	1	Painted	Painted
30702-045	2U	Anodized	Screw-on Front	1	Raw	Raw
30702-048	2U	Anodized	Screw-on Front	1	Anodized	Anodized
30702-057	2U	Powder Coated	Screw-on Front	1	Painted	Painted
30118-964	3U	Powder Coated	Screw-on Front	1	Painted	Painted
30702-046	3U	Anodized	Screw-on Front	1	Raw	Raw
30702-049	3U	Anodized	Screw-on Front	1	Anodized	Anodized
30702-058	3U	Powder Coated	Screw-on Front	1	Painted	Painted

Table 2/3						
Catalog Number	Treated Edges	Color Code	EMC Shielding	Высота мм (Н)	Туре	Ширина мм (W)
30118-962		RAL 7021	Нет	43.6mm	19" Front Panel	483mm
30702-044			Нет	43.6mm	19" Front Panel	483mm
30702-047	Да		Нет	43.6mm	19" Front Panel	483mm
30702-056		RAL 7035	Нет	43.6mm	19" Front Panel	483mm
30118-963		RAL 7021	Нет	88.1mm	19" Front Panel	483mm
30702-045			Нет	88.1mm	19" Front Panel	483mm

CatalogNumber	Treated Edges	Color Code	EMC Shielding	Высота мм (Н)	Туре	Ширина мм(W)
30702-048	Да		Нет	88.1mm	19" Front Panel	483mm
30702-057		RAL 7035	Нет	88.1mm	19" Front Panel	483mm
30118-964		RAL 7021	Нет	132.5mm	19" Front Panel	483mm
30702-046			Нет	132.5mm	19" Front Panel	483mm
30702-049	Да		Нет	132.5mm	19" Front Panel	483mm
30702-058		RAL 7035	Нет	132.5mm	19" Front Panel	483mm


Table 3/3				
Catalog Number	Quick Ship			
30118-962	No			
30702-044	No			
30702-047	No			
30702-056	No			
30118-963	No			
30702-045	No			
30702-048	No			
30702-057	No			
30118-964	No			
30702-046	No			
30702-049	No			

Catalog Number	Quick Ship
30702-058	No

ADDITIONAL PRODUCT DETAILS

Монтажный комплект для сборки на 19 дюймов заказывается отдельно.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



This document is system-generated.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE