


Инструменты для компонентов повышенной прочности



Детали для сборки с резьбовым соединением для прочной боковой панели, горизонтальной рейки, заглушек, заднего уголка.

CERTIFICATIONS



FEATURES

Винты для следующих креплений: прочная боковая панель — горизонтальная рейка, Прочная боковая панель — заглушка, прочная боковая панель — задний уголок

SPECIFICATIONS

Product Type: Монтажные детали

Product Family: EuropacPRO

Table 1/2

Catalog Number	Type	Длина мм	Package Quantity	Thread Size	Finish	Material
24566-105	Countersunk Screw	7mm	100	M4		Нержавеющая сталь
24560-140	Square Nut		100		Zinc Plated	Сталь
24566-106	Countersunk Screw	10mm	100	M4		Нержавеющая сталь

CatalogNumber	Type	Длина мм	Package Quantity	Thread Size	Finish	Material
24566-101	Countersunk Screw	14mm	100	M4		Нержавеющая сталь
24566-100	Countersunk Screw	18mm	100	M4		Нержавеющая сталь
24566-104	Panhead Screw	8mm	100	M4		Нержавеющая сталь
24566-103	Panhead Screw	10mm	100	M4		Нержавеющая сталь
24566-102	Panhead Screw	14mm	100	M4		Нержавеющая сталь

Table 2/2

Catalog Number	Works With	Quick Ship
24566-105	Блочный каркас	No
24560-140	Блочный каркас	No
24566-106	Блочный каркас	No
24566-101	Блочный каркас	No
24566-100	Блочный каркас	No
24566-104	Блочный каркас	No
24566-103	Блочный каркас	No
24566-102	Блочный каркас	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE