

Front Panel, Flat, With Slot for Stainless Steel EMC Gasket



Front panel, flat, with slot for stainless steel EMC gasket.

CERTIFICATIONS



CARACTERISTICI

Flat front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For stainless steel gasket

SPECIFICAȚII

Depth:	2.5mm
Rack Height:	4U
Material:	Aluminiu
Finish:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel without Handle
EMC Shielding:	No (Retrofittable)

Table 1/2

Număr de catalog	Rack Width	Package Quantity	Mounting	EMC Gasket Type	Front Finish	Rear Finish
------------------	------------	------------------	----------	-----------------	--------------	-------------

30846-681	42HP	1	Screw-on Front	Stainless Steel	Anodized	Conductive
30846-682	63HP	1	Screw-on Front	Stainless Steel	Anodized	Conductive

Table 2/2

Număr de catalog	Treated Edges	Complies With	Height	Width	Quick Ship
30846-681	No	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	213mm	No
30846-682	No	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	319.7mm	No

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE