


Комплект для комбинированного монтажа для шасси



Комбинированный монтаж позволяет разделить блочный каркас или корпус высотой 6 U на секции 2 x 3 U и 6 U. Доступны различные варианты.

CERTIFICATIONS



FEATURES

Для стандартных европлат (высотой 100 мм) и для европлат двойной высоты (высотой 233,35 мм)

Монтажное пространство высотой 6 U разделено на секции: 2 x 3 U, 1 x 6 U

SPECIFICATIONS

Rack Height:	6U
Type:	Combined
Product Family:	EuropacPRO
Product Type:	Mounting Kit
Works With:	Блочный каркас

Table 1/1

Catalog Number	Package Quantity	Rack Width 1	Rack Width 2	Material	Quick Ship
24562-420	1	20HP	62HP	Алюминий, Zinc Alloy	No
24562-440	1	40HP	42HP	Алюминий, Zinc Alloy	No

Catalog Number	Package Quantity	Rack Width 1	Rack Width 2	Material	Quick Ship
24562-442	1	42HP	40HP	Алюминий, Zinc Alloy	No
24562-484	1	84HP		Алюминий, Zinc Alloy	No
24562-463	1	63HP	19HP	Алюминий, Zinc Alloy	No

ADDITIONAL PRODUCT DETAILS

Please order separately: Передняя панель 6 U, 2 HP to cover the strut.

The following guide rails cannot be used: type "accessory", type "accessory, strengthened" and type "for 4,4" PCB".

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE