

19-дюймовый блок вентилятора, 1 U, дистанц. управление и мониторинг, 6 вентиляторов, 100–240 В перем. тока

CATALOG NUMBER

10713-554



Вентиляторный блок с интерфейсом ModBus для установки в пространство 1 U внутри шкафа

CERTIFICATIONS



FEATURES

Управление скоростью и температурой вентилятора

Интерфейс ModBus для дистанционного мониторинга и управления

Температурная граница для управления вентилятором, регулируемый на передней панели

Сигнализация при выходе из строя и перегреве вентилятора 2 светодиодами и беспотенциальными выходными реле

Встроенный источник питания с широким диапазоном входного напряжения (100–240 В)

Менее 1 U (42 мм) для возможности монтажа на направляющих или ящике

Датчики температуры 2 NTC с кабелями

PRODUCT ATTRIBUTES

Product Type: Fan Unit

Input Voltage AC: 100 – 240V

Airflow: 1089m³/h

Noise Level: 59.5dB(A)

Мощность W: 97W

Max Static Pressure: 78Pa

Ambient Temperature: -10 to 70°C

Lifespan, L10 @ 40 C: 99558h

Package Quantity: 1

Finish: Aluminum-Zinc Plated; Anodized

Gross Weight: 5.2kg

Material: Сталь; Алюминий

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE