


Система VXS, Tower, 5 U, 7 слотов, вставной ИСТОЧНИК ПИТАНИЯ

CATALOG NUMBER

10836-060



Система Tower для 7 VXS печатных плат 6 U, глубина 160 мм. Возможна установка задней панели ввода-вывода. Питание системы осуществляется вставным блоком питания.

CERTIFICATIONS



FEATURES

Система в соответствии с IEC60297-3-101, -102, -103 IEEE 1101.1, 1101.10/11; объединительная панель, в соответствии с VITA 41.0, -41,1, -41,10, -41,11

Блоки питания, 19" совместимый, 250 Вт; дополнительно возможна установка второго блока питания

Объединительная плата VXS/VME64x4 слота VME64x, 6 U, с разъемом P03 слота VXS Payload, подключенные «кольцом»

Отвод тепла 4 вентиляторами, отвод тепла спереди назад; управление температурой при помощи модуля управления вентиляторами (FCM)

Модуль индикации рабочего напряжения (пост. ток), аварийные сигналы от вентиляторов и датчиков температуры

PRODUCT ATTRIBUTES

Product Type: System
Глубина мм: 300mm
Высота мм: 496.25mm
Ширина мм: 221.45mm
Мощность W: 250W

ADDITIONAL PRODUCT DETAILS

Модифицированные системы доступны по запросу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE