


RatiopacPro Tip-Up Handle Assembly Kit

The assembly kit must be used if a tip-up handle should be mounted. Standard side covers should be replaced.



CERTIFICATIONS



CARACTERISTICI

Aluminum side panel powder coated RAL 9006, Adapter and assembly material.

SPECIFICAȚII

Product Type:	Assembly Kit
Works With:	Cases
Product Family:	RatiopacPRO; RatiopacPRO AIR
Type:	Tip-Up Handle Kit

Table 1/2

Număr de catalog	Rack Height	Rack Width	Depth	Package Quantity	Finish	Material
24571-352	3U	42HP	255mm	2	Vopsit Pulbere	Aluminiu
24571-353	3U	42HP	315mm	2	Vopsit Pulbere	Aluminiu
24571-354	3U	42HP	375mm	2	Vopsit Pulbere	Aluminiu

Număr de catalog	Rack Height	Rack Width	Depth	Package Quantity	Finish	Material
24571-355	3U	42HP	435mm	2	Vopsit Pulbere	Aluminiu
24571-356	3U	42HP	495mm	2	Vopsit Pulbere	Aluminiu
24571-359	4U	42HP	255mm	2	Vopsit Pulbere	Aluminiu
24571-360	4U	42HP	315mm	2	Vopsit Pulbere	Aluminiu
24571-361	4U	42HP	375mm	2	Vopsit Pulbere	Aluminiu
24571-362	4U	42HP	435mm	2	Vopsit Pulbere	Aluminiu
24571-363	4U	42HP	495mm	2	Vopsit Pulbere	Aluminiu

Table 2/2

Număr de catalog	Quick Ship
24571-352	No
24571-353	No
24571-354	No
24571-355	No
24571-356	No
24571-359	No
24571-360	No
24571-361	No
24571-362	No
24571-363	No

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE