


Пластиковая ручка статическая трапецевидной формы, серая, ширина 12 HP

CATALOG NUMBER

20808-064



Статическая пластиковая ручка трапецевидной формы серого цвета может быть установлена на лицевую панель для извлечения печатной платы.

CERTIFICATIONS



FEATURES

С отдельной идентификационной табличкой, алюминий 1,5 мм

Ручка, поликарбонат, UL 94 V-0

PRODUCT ATTRIBUTES

Rack Width: 12HP

Package Quantity: 1

Handle Type: Трапецевидной ручкой, антистатическ

Flammability Rating: UL® 94V-0

Color: Light Grey

Color Code: RAL 7035

Complies With: EN 45545-2, R22-R24, HL3; IEC 60297-3-101

Глубина мм (D): 14mm

Высота мм (H): 15.4mm

Material: Polyphenylene Ether

Product Type: Ручка

Type: Static

Ширина мм (W): 59.6mm


Works With: Передние панели

ADDITIONAL PRODUCT DETAILS

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

Не может использоваться вместе с фиксирующим зажимом (21101-239).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE