


AirBender, вставка для направляющей карты, блокировка 70P, 4HP, 160 мм

CATALOG NUMBER

24563-040



Вставка AirBender от компании nVent SCHROFF повышает эффективность охлаждения до 85 % на каждый слот за счет балансировки воздушного потока в средах со смешанным сопротивлением. Она проста в установке, снижает шум вентиляторов и повышает общую производительность системы.

FEATURES

Направляющие вставки для плат AirBender повышают эффективность охлаждения электронных систем до 85 % на каждый слот шириной 4HP за счет балансировки воздушного потока в средах со смешанным сопротивлением воздуха

Блокировка 70 %: AirBender обеспечивает дополнительное сопротивление воздуха в слотах с менее критичными компонентами, перенаправляя поток воздуха в более уязвимые зоны и обеспечивая лучшее охлаждение всех плат

Простота установки: просто вставьте устройство AirBender в пластиковые направляющие для плат nVent SCHROFF и дополнительно закрепите его винтом

Способствует снижению уровня шума, производимого вентиляторами, поддерживая их в эффективном рабочем состоянии

Air bender and CassettePRO cannot be used together in the same slot.

PRODUCT ATTRIBUTES

Product Type: Air Baffle

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac

Works With: Блочный каркас; Coffrets; Системы

Rack Width: 4HP

Глубина мм: 160mm

Material: Polycarbonate

Package Quantity: 10

Color: Серый

Complies With: EN 45545-2; UL® 94V-0

ADDITIONAL PRODUCT DETAILS

По запросу доступны устройства AirBender с различными уровнями блокировки.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE