


Направляющие типа «принадлежность» для тяжелых печатных плат, особо прочные, алюминиевые, 160 мм, ширина канавки 2 мм, серебристые, 10 шт.

CATALOG NUMBER

34562-881



This reinforced guide rail for heavy PCBs of the type accessory, forms a reliable interface between the subrack mechanics and the sub-assemblies. The guide rails can additionally be bolted to the horizontal

CERTIFICATIONS



FEATURES

Для особо тяжелых печатных плат, вставных модулей или кассет

Крепление, для винтового крепления к горизонтальным рейкам только типа H (прочные) и типа R (повышенной прочности)

Алюминиевый профиль

PRODUCT ATTRIBUTES

Package Quantity: 1

Board Depth: 160mm

Groove Width: 2

Color: Серебристый

Finish: Anodized

Material: Алюминий

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac

Product Type: Направляющие рельсы

Type: Heavy Duty

Works With: Блочный каркас; Coffrets; Chassis

Net Weight: 0.014kg

ADDITIONAL PRODUCT DETAILS

Доставка осуществляется исключительно в количестве стандартной упаковки.

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE