


Регулируемый кронштейн монитора с подставкой для клавиатуры (Vamonitor)

CATALOG NUMBER

60118-563



Подвесной кронштейн с подставкой для клавиатуры с высокой гибкостью и возможностью подключения HMI для оператора. Складной шарнирный кронштейн идеально подходит для рабочей станции, установленной в шкафу. Это простое в установке, монтируемое в шкаф приспособление, которое обеспечивает панорамные возможности установки плоскостной панели монитора, клавиатуры и мыши в промышленных условиях.

FEATURES

Опорный кронштейн для крепления плоскостной панели монитора, клавиатуры и мыши

Крепление осуществляется сбоку от сверхпрочной рамы

Допустимая статическая нагрузка кронштейна не более 8 кг, Допустимая статическая нагрузка клавиатуры не более 2,5 кг

Опорный кронштейн: регулируется по высоте 300 мм; угол поворота на корпусе 180°; угол поворота монитора 340° (установлен на корпусе 270°); угол наклона монитора 60°; интегрированная кабельная разводка

Подходит для промышленного и лабораторного применения

Место для хранения клавиатуры и мыши

PRODUCT ATTRIBUTES

Product Type: Monitor Arm
Works With: Cabinet
Material: Сталь; Алюминий; Plastic
Net Weight: 11.8kg
Package Quantity: 1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE