


Пластиковая ножка



Пластмассовый материал откидных ножек позволяет выполнять установку на нижней панели корпуса. Ножки могут быть откидные или неоткидные. Исполнены в черном или сером цвете.

CERTIFICATIONS



FEATURES

Можно использовать вместо стандартных круглых ножек

Допустимая нагрузка: 25 кг на ножку, максимальный вес корпуса 40 кг

В нижних крышках корпусов предусмотрены монтажные отверстия

Устойчивое положение корпуса за счет нескользащих резиновых вставок

SPECIFICATIONS

Works With:	Coffrets
Product Family:	RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac
Type:	Ножка; With Tip-up
Product Type:	Ножка
Material:	Polyamide

Table 1/1

Catalog Number	Package Quantity	Quick Ship
10603-023	1	No
10603-026	1	No

Catalog Number	Package Quantity	Quick Ship
10603-025	1	No
10603-024	1	No

ADDITIONAL PRODUCT DETAILS

Поставка исключительно в размере товарной партии. Цена указана за отдельную единицу.

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE