


Комплект вставного блока для РМС, хроматированная, Экранированный (текстиль) с ручкой



U-образная передняя панель с вырезом для РМС.
Возможность экранирования тканевой ЭМС-прокладкой.

FEATURES

В соответствии с требованиями IEEE P1386, мезонинная плата PCI

Для одиночного модуля 69,0 x 76,5 мм или двойного модуля 139,0 x 76,5 мм

Для стандартных мезонинных модулей ввода/вывода, которые подключаются к платам носителя

РМС = мезонинная плата PCI

ПЛИС = программируемая логическая интегральная схема

Передняя панель из U-образного профиля 3 U, 4 HP, с текстильным уплотнителем

ЭМС-экранирование передней панели и крышек для вырезов передней панели

SPECIFICATIONS

Rack Width:	4HP
Material:	Алюминий
Product Type:	Передняя панель
Type:	Front Panel with Handle (PIU)

EMC Shielding: Да

Table 1/2

Catalog Number	Rack Height	Package Quantity	Handle Type	Mounting	Gasket Type	Front Finish
20836-460	3U	1	IEL	Screw-on Front	Textile EMC	Anodized
20836-461	6U	1	IEL	Screw-on Front	Textile EMC	Anodized

Table 2/2

Catalog Number	Rear Finish	Complies With	Finish	Quick Ship
20836-460	Conductive	Мезионная PMC, IEEE P1386	Anodized, Passivated	No
20836-461	Conductive	Мезионная PMC, IEEE P1386	Anodized, Passivated	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE