

панель электропитания, IEC, 3-фазный



Компактная модульная конструкция панели электропитания с множеством функциональных элементов. Распределительный блок питания на алюминиевом шасси размером 1 U x 1 U легко интегрируется в шкаф с розетками IEC C13 и C19 с 3-фазным входом.

CERTIFICATIONS



FEATURES

Блок розеток с розетками IEC в соответствии с IEC 60320

Вертикальный монтаж

При установке панель электропитания можно развернуть в любую сторону (с шагом 90°)

Сетевой кабель 2 м

Монтажная высота 1 U

Монтажная высота 1 U

SPECIFICATIONS

Material:	Алюминий; Polyamide
Color:	Серый; Черный; Красный
Product Type:	Панели электропитания

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Package Quantity	Глубина мм
60110-285	IEC C13, IEC C19	30	Нет	400V	1	44mm

CatalogNumber	Socket Type	SocketQuantity	Switched Outlets	Voltage AC	Package Quantity	Глубина мм
60110-283	IEC C13	18	Нет	400V	1	44mm
60110-284	IEC C13, IEC C19	24	Нет	400V	1	44mm

Table 2/2				
Catalog Number	Finish	Высота мм	Длина мм	Quick Ship
60110-285	Anodized	44mm	1753mm	No
60110-283	Anodized	44mm	947.5mm	No
60110-284	Anodized	44mm	947.5mm	No

ADDITIONAL PRODUCT DETAILS

Кронштейн для вертикального монтажа заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE