

Varistar CP Top Rear Panel, Укороченная



Укороченная задняя панель доступна для применения в системах IP20, IP55.

Укороченные задние панели обеспечивают эффективную организацию укладки кабелей.

FEATURES

Крепление на винтах, прочная боковая панель для монтажа одним человеком

Высота соединительной панели составляет 400 мм

SPECIFICATIONS

Product Type: Cabinet Door
Protection Rating: IP55
Material: Сталь

Table 1/2

Catalog Number	Rack Height	Высота мм	Ширина мм	Package Quantity	Color	Color Code
21630-360	38U	1800mm	600mm	1	Black Grey	RAL 7021
21630-362	42U	2000mm	600mm	1	Black Grey	RAL 7021
21630-364	47U	2200mm	600mm	1	Black Grey	RAL 7021
21630-361	38U	1800mm	800mm	1	Black Grey	RAL 7021
21630-363	42U	2000mm	800mm	1	Black Grey	RAL 7021

CatalogNumber	Rack Height	Высота мм	Ширина мм	Package Quantity	Color	Color Code
21630-365	47U	2200mm	800mm	1	Black Grey	RAL 7021

Table 2/2

Catalog Number	Finish	Quick Ship
21630-360	Powder Coated	No
21630-362	Powder Coated	No
21630-364	Powder Coated	No
21630-361	Powder Coated	No
21630-363	Powder Coated	No
21630-365	Powder Coated	No

ADDITIONAL PRODUCT DETAILS

Высота задней панели на 400 мм меньше высоты шкафа, что позволяет размещать соединительную панель.

Комплект заземления можно приобрести отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE