

Intelligent iPDU, EN6880, 400 VAC, 3-PH, 32 A

Data Solutions

CATALOG NUMBER

EN6880



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

FEATURES

Enlogic EN6xxx Intelligent Power Distribution Units monitors input power and power of each individual outlet and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

PRODUCT ATTRIBUTES

Product Family: Enlogic

Type: Интеллектуальные PDU

Product Type: Панели электропитания

Socket Type: (21) Locking C13/C15; (21) Locking C13/C15/C19/C21

Socket Quantity: 42

Color: Черный

Circuit Breaker: 20 A, 1-pole, Hy-Mag

Switched Outlets: Да

Circuit Breaker Quantity: 6

Power Rating: 17.3 kVA North America; 22.1 kVA International

Input Cable Location: Top Feed

Max Power Input: 17.3 / 22.1 kVA

Input Voltage: 380 – 415V

Phase: 3 PH

On/Off Switch Included: Да

Nominal Voltage: 415V

Output Voltage: 208 – 230VAC

Plug Type: IEC 60309 530P6/532P6

Amperage (Derated Amperage): 30 A (24 A) North America; 32 A International

Removable Input Cable: Нет

Rack Units: 0U

Material: Сталь

Finish: Powder Coated

Metering Type: Outlet

Высота мм: 1780mm

Ширина мм: 56mm

Глубина мм: 75mm

Weight: 11.62kg

Package Quantity: 1

Input Cable Length: 1.8m

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE