

Шкаф Comline ECL для установки вне помещений

Data Solutions



Для телекоммуникационной и железнодорожной отраслей требуется установка сложной электроники вне помещений. Шкафы nVent SCHROFF Outdoor защищают эти электронные компоненты от экстремальных погодных условий и вандализма, обеспечивая бесперебойную работу.

CERTIFICATIONS



FEATURES

IP55

Отвод тепла за счет естественной конвекции

Облегченный, алюминиевый шкаф с одинарными стенками

SPECIFICATIONS

Material: Алюминий

Table 1/3

Catalog Number	Product Type	Product Family	Rack Height	Высота мм	Ширина мм	Глубина мм
12349-001	Outdoor Cabinet	Comline ECL	12U	600mm	600mm	500mm

CatalogNumber	Product Type	Product Family	Rack Height	Высота мм	Ширина мм	Глубина мм
12349-002	Outdoor Cabinet	Comline ECL	18U	900mm	600mm	500mm
12349-003	Outdoor Cabinet	Comline ECL	18U	900mm	700mm	600mm
12349-004	Outdoor Cabinet	Comline ECL	25U	1200mm	700mm	600mm
12349-009	Outdoor Cabinet	Comline ECL	12U	600mm	600mm	500mm
12349-010	Outdoor Cabinet	Comline ECL	18U	900mm	600mm	500mm
12349-011	Outdoor Cabinet	Comline ECL	18U	900mm	700mm	600mm
12349-012	Outdoor Cabinet	Comline ECL	25U	1200mm	700mm	600mm

Table 2/3

Catalog Number	Wall Type	Door Type	Access	Cooling	EMC Shielding	Complies With
12349-001	Single Walled	Single Door	С передней стороны	Natural Convection	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-002	Single Walled	Single Door	С передней стороны	Natural Convection	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-003	Single Walled	Single Door	С передней стороны	Natural Convection	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

CatalogNumber	Wall Type	Door Type	Access	Cooling	EMC Shielding	Complies With
12349-004	Single Walled	Single Door	С передней стороны	Natural Convection	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-009	Single Walled	Single Door	С передней стороны	Natural Convection	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-010	Single Walled	Single Door	С передней стороны	Natural Convection	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-011	Single Walled	Single Door	С передней стороны	Natural Convection	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-012	Single Walled	Single Door	С передней стороны	Natural Convection	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

Table 3/3

Catalog Number	Package Quantity	Finish
12349-001	1	Powder Coated
12349-002	1	Powder Coated

Catalog Number	Package Quantity	Finish
12349-003	1	Powder Coated
12349-004	1	Powder Coated
12349-009	1	Powder Coated
12349-010	1	Powder Coated
12349-011	1	Powder Coated
12349-012	1	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE