


Бортовой шкаф, высота 3 U, ширина стойки 84 HP

CATALOG NUMBER

10170-014



Подходит для применения в условиях постоянных вибраций, ударов, высоких температур и высокой влажности.

CERTIFICATIONS



FEATURES

Для передвижного железнодорожного оборудования

Подходит для использования в условиях постоянных вибраций, ударной нагрузки, высоких температур, и высокой влажности

Подходит для блочных каркасов высотой 1, 2, or 3 U SNCF sub racks (NF F61-005, CF 60-002)

Задняя сторона предназначена для стандартных разъемов; траверса может быть сконфигурирована для кодовых штифтов SNCF

Траверса со встроенным кабельным каналом

Несколько стоек можно штабелировать или смонтировать в ряд

Произведена с использованием сварочного процесса, certified to EN 15085 (CL2)

Stainless Steel welds passivated to prevent corrosion

PRODUCT ATTRIBUTES

Product Family: Стойка на плате

Rack Height: 3U

Высота мм: 156.7mm

Rack Width: 84HP

Ширина мм: 496.4mm

Package Quantity: 1

Complies With: SNCF NFF 61005; SNCF NFF 60002

Глубина мм: 341.8mm

Frame Material: Сталь

Material: Нержавеющая сталь

Product Type: Rack

Static Load: 25kg

Gross Weight: 4.35kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE