

Front Panel EMC Textile Shielding Kit, - 40...+70°C, 6 U, 10 шт.

CATALOG NUMBER

21101-855



Текстильные ЭМС-прокладки вставляются в слот с правой стороны U-образных передних панелей. Прокладки приклеиваются к передней панели.

CERTIFICATIONS



FEATURES

Текстильный ЭМС-уплотнитель крепится сбоку на передней панели или при необходимости в пазу правого профиля.

Профильное уплотнение наклеивается на контактную поверхность 19-дюймового кронштейна или заднего угла и устанавливает токопроводящее соединение с U-образными передними панелями.

Диапазон температур -40 °C.. +70 °C

PRODUCT ATTRIBUTES

Rack Height: 6U

Package Quantity: 10

Глубина мм (D): 1.62mm

Высота мм (H): 232mm

Material: Thermoplastic Elastomer

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; PropacPRO; Frame Type Plug-In Unit

Product Type: Shielding Kit

Ширина мм (W): 3.8mm

Works With: Блочный каркас; Coffrets; Передние панели


Flammability Rating: UL® 94V-0

Gross Weight: 0.092kg

ADDITIONAL PRODUCT DETAILS

ЭМС-прокладки (текстильные) необходимы для экранирования передних панелей.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE