

Varistar CP Cabinet Frame, Seismic Heavy Load

Power Utilities

Welded, steel enclosure engineered specifically to protect equipment in areas with seismic activity and satisfy Bellcore Zore 4 requirements.

FEATURES

St, 1.5 mm, zinc-plated, finish: powder-coated

Earthquake resistance to Bellcore Zone 4

Welded heavy-duty frame with strengthening brackets, RAL 7021

Dynamic load-carrying capacity 500 kg to IEC 61587-2

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Height	Width	Depth	Shock and Vibration Tolerance	Color
20630-269	42 U	2000 mm	600 mm	1000 mm	5 g (force)	Black Grey
20630-270	42 U	2000 mm	600 mm	1200 mm	5 g (force)	Black Grey
20630-271	42 U	2000 mm	800 mm	1000 mm	5 g (force)	Black Grey
20630-272	42 U	2000 mm	800 mm	1200 mm	5 g (force)	Black Grey
20630-273	33 U	1600 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-274	33 U	1600 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-275	33 U	1600 mm	800 mm	600 mm	5 g (force)	Black Grey

CatalogNumber	Rack Height	Height	Width	Depth	Shock and Vibration Tolerance	Color
20630-276	33 U	1600 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-277	38 U	1800 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-278	38 U	1800 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-279	38 U	1800 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-280	38 U	1800 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-281	42 U	2000 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-282	42 U	2000 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-283	42 U	2000 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-284	42 U	2000 mm	800 mm	1600 mm	5 g (force)	Black Grey
20630-285	42 U	2200 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-286	47 U	2200 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-287	47 U	2200 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-288	47 U	2200 mm	800 mm	800 mm	5 g (force)	Black Grey

Table 2/3

Catalog Number	Color Code	Complies With	Frame Material	Material	Product Type	Static Load
20630-269	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-270	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-271	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf

CatalogNumber	Color Code	Complies With	Frame Material	Material	Product Type	Static Load
20630-272	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-273	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-274	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-275	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-276	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-277	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-278	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-279	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-280	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-281	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-282	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-283	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-284	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-285	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-286	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-287	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-288	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf

Table 3/3

Catalog Number	Type	Works With
----------------	------	------------

20630-269	Heavy Load	Varistar CP
20630-270	Heavy Load	
20630-271	Heavy Load	Varistar CP
20630-272	Heavy Load	Varistar CP
20630-273	Heavy Load	Varistar CP
20630-274	Heavy Load	Varistar CP
20630-275	Heavy Load	Varistar CP
20630-276	Heavy Load	Varistar CP
20630-277	Heavy Load	Varistar CP
20630-278	Heavy Load	Varistar CP
20630-279	Heavy Load	Varistar CP
20630-280	Heavy Load	Varistar CP
20630-281	Heavy Load	Varistar CP
20630-282	Heavy Load	Varistar CP
20630-283	Heavy Load	Varistar CP
20630-284	Heavy Load	Varistar CP
20630-285	Heavy Load	Varistar CP
20630-286	Heavy Load	Varistar CP
20630-287	Heavy Load	Varistar CP

20630-288	Heavy Load	Varistar CP
-----------	------------	-------------

ADDITIONAL PRODUCT DETAILS

Please order attachments and components separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE