

# Connection Kit, Cold Applied, for PI Heaters, ATEX



nVent RAYCHEM CS-150-xx-PI are a range of low profile, under-insulation power connection or splice for polymer insulated (PI) series heating cables, using two component silicone compound to provide durable and flexible moisture proof encapsulation. Available in 3 versions, to allow robust & reliable connections up to 125A and approved for use in hazardous area. The internal electrical connection is by nickel plated crimps, specifically designed to provide reliable electrical connections over a very wide temperature range.

## FEATURES

Simple and fast to install

Cold applied: no heat gun, no hot work permit needed

Low profile, under-insulation component

Unique design, to ensure optimum connection reliability

Approved for use in hazardous areas

## SPECIFICATIONS

<b>Max Operating Temperature:</b>	200 °C
<b>Voltage Rating:</b>	750 V max
<b>Connection Type:</b>	Cold Applied
<b>Area Classification:</b>	Non-Hazardous; Hazardous
<b>IP Rating:</b>	IP65

Table 1/1

Catalog Number	Item Name	Current Rating	Suitable for Cold Lead
1244-000588	CS-150-6-PI	54 A	4 – 6 mm <sup>2</sup>
1244-000587	CS-150-25-PI	129 A	10 – 25 mm <sup>2</sup>
1244-000586	CS-150-2.5-PI	32 A	0 – 2.5 mm <sup>2</sup>

## ADDITIONAL PRODUCT DETAILS

---

Attribute Current Rating is applicable when used as hot-cold joint.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East,

#### Africa

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM** **PYROTENAX** **TRACER** **NUHEAT**