




Тестовые адаптеры для VMEbus, P2, высота 3 U, 160 мм

CATALOG NUMBER

23021-100



Тестовый адаптер для плат VMEbus для доступа к контрольным точкам на печатной плате.

CERTIFICATIONS



FEATURES

Маршрутизация и укладка слоев соответствуют требованиям шины VME

Для измерения тока и напряжения (V/I), (a)

Дополнительные измерительные контакты, например, для измерительных наконечников осциллоскопа (b)

1 slot для второго испытываемого прибора, 1 slot для платы согласования

Тестовые адаптеры 6 U состоят из двух тестовых адаптеров 3 U, соединенных промежуточным адаптером

Линии подачи напряжения рассчитаны на 2 A

PRODUCT ATTRIBUTES

Product Type: Test Adapter

Type: VMEbus

Connector Type: C96, I/O Bus

Board Depth: 160mm

Rack Height: 3U

Measuring Field: Current; Voltage

Number of Layers: 6

Net Weight: 0.496kg

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Информация по испытательному адаптеру 9 U VMEbus приводится в описании кронштейна промежуточного адаптера, 9 U, 220 мм, 350 мм.

P1 = шина системы, P2 = шина ввода/вывода.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE